

Search Results

- Evaluate
  - FAQ's
- Design a Solution
  - Part Drawings
  - PDFRing Termina..
- How to Buy
  - Bill of Material
  - Favorite Products List
  - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips

 Text Search: 'P8-8RNHT6-Q'

Your search criteria matched only one product, shown below

**P8-8RNHT6-Q**



- Nickel plated copper for temperatures up to 650°F (343°C)
- Internal barrel serrations assure good wire contact and maximum tensile strength
- Brazed seam protects terminal barrel from splitting during the crimp process
- Barrel of terminal internally beveled to provide quick and easy wire insertion
- Rated up to 2000 V

Part Number	P8-8RNHT6Q
RoHS Compliancy Status	Compliant
Part Description	High Temperature Ring Terminal, 8 AWG, #8 stud size, noninsulated, narrow tongue.
Product Type	Terminals
CSA Certified	Pending
UL Listed	Yes
Length (In.)	1.09
Length (mm)	27.7
Width (In.)	0.36
Width (mm)	9.3
CE Compliant	No
Clearance	0.43
Clearance (mm)	10.9
Insulation	non-insulated
Plating Type	Nickel
Pricing Description	Ring Terminal, high temperature, noninsulated, 8 awg, #8 stud size, narrow
Stock	0.04
Stock (mm)	1.0
Stud Size	#8
Tool	CT-2600, CD-2600-8†
Wire Range	8 AWG
Wire Range (mm²)	10
Min. Order UOM	PC
Min. Order Qty.	25
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	<input type="button" value="e"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.