



Search by part # or keyword

[Products](#)

[Industries & Solutions](#)

[Resources](#)

[TE Store](#)


[Sign In](#)



[Harnessing](#) > [Heat Shrink Components](#) > [Heat Shrink Boots](#)

# 202K163-100-01-0

202K163-100-01-0



Raychem

TE Internal #: **313427-000**

TE Internal Description: **202K163-100-01-0**

Alias #: **9-1192370-6**

Molded Part Shape : **Straight**

Molded Part Shape Code : **202**

Lipped : **Yes**

Material Code : **100**

Material Systems Code : **100**

[Compatible Parts & Tooling](#)

### We are here to help!

Get in touch with our product experts.



[CHAT WITH US](#)



[EMAIL US](#)



[CALL US](#)

Feedback

#### Documents

#### Features

#### Product Compliance

##### Product Drawings

##### Dimensional Drawing

202K163-100-01-0

[202K163-100-01-0](#) English

##### Datasheets & Catalog Pages

1654025\_Sec4\_-100

[ENG\\_CS\\_1654025\\_Sec4\\_-100\\_0313.pdf](#) English

##### Product Specifications

##### Product Specification

[ENG\\_SS\\_RT-1323\\_1.pdf](#) English

##### Product Environmental Compliance

##### Safety Datasheet

[ENG\\_MSDS\\_RAY3146-CA-ENG\\_C.pdf](#) English

[DAN\\_MSDS\\_RAY3146-EC-DAN\\_A.pdf](#) Danish

##### Safety Datasheet

[DUT\\_MSDS\\_RAY3146-EC-DUT\\_A.pdf](#) Dutch

##### Safety Datasheet

[ENG\\_MSDS\\_RAY3146-EC-ENG\\_A.pdf](#) English

##### Safety Datasheet

[FRE\\_MSDS\\_RAY3146-EC-FRE\\_A.pdf](#) French

##### Safety Datasheet

[GER\\_MSDS\\_RAY3146-EC-GER\\_A.pdf](#) German

##### Safety Datasheet

[ITA\\_MSDS\\_RAY3146-EC-ITA\\_A.pdf](#) Italian

##### Safety Datasheet



[NOR\\_MSDS\\_RAY3146-EC-NOR\\_A.pdf](#) Norwegian

Safety Datasheet

[SPA\\_MSDS\\_RAY3146-EC-SPA\\_A.pdf](#) Spanish

Safety Datasheet

[SWE\\_MSDS\\_RAY3146-EC-SWE\\_A.pdf](#) Swedish

Safety Datasheet

[ENG\\_MSDS\\_RAY3146-US-ENG\\_C.pdf](#) English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features Molded Part Shape : **Straight**

Configuration Features Lipped : **Yes**

Body Features Material Code : **100**  
Material Systems Code : **100**  
Adhesive Pre-Coat : **No**  
Material : **Low Fire Hazard Material**

Dimensions Cable Diameter Range : **9.9 – 22 mm [ 9.9 – 23 in ]**  
Wire/Cable Outside Diameter :  
**.43 in, .433 in, .47 in, .55 in, .63 in, 11 mm, 12 mm, 14 mm, 16 mm**

Usage Conditions Operating Temperature Range : **-30 – 105 °C [ -22 – 221 °F ]**  
Flammability : **Low Fire Hazard**

Operation/Application Power Cable Accessory : **No**

Industry Standards Approved Standards :  
**BR1326 listed Class G, BS-G-198-5-DF, DEF Std 59-97 Issue 3 Type DF, IEC 62329-3-101, VG95343 Part 28**  
Government Qualified : **No**

Other Molded Part Shape Code : **202**  
Fluid/Chemical Resistance :  
**Long-Term Exposure at High Temperature**  
Adhesive Options : **/180 Precoat**  
Adhesive Type : **Adhesive Purchased Separately**

Detailed product compliance is not available. Please [Contact Us](#)

Statement of Compliance [Statement of Compliance pdf](#)

[ABOUT TE CONNECTIVITY](#)

[FOR PARTNERS](#)

[SUPPORT](#)

[CALL US](#)

[LIVE CHAT](#)

[UNITED STATES \(EN\)](#)