


Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Catalog Cut Sheet
 - PDFPV18-4RX-CY
 - PDFPV14-8RX-C P
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips

 Text Search: 'PV14-56RX-L'

Your search criteria matched only one product, shown below

PV14-56RX-L



- Expanded wire entry designed to accommodate wire with a larger insulation thickness
 - Ring tongue design assures a secure connection in high vibration applications
 - Insulation support helps to prevent wire damage in bending applications
 - Brazed seam protects terminal barrel from splitting during the crimp process
 - Internal barrel serrations assure good wire contact and maximum tensile strength
 - UL Flammability UL 94V -0, maximum insulation temperature 221°F (105°C)
 - UL and CSA rated up to 600 V per UL 486A/B
- ‡UL and CSA approved tooling/product combinations.

Part Number	PV14-56RX-L
RoHS Compliance Status	Compliant
Note	PV14-56RX-L replaces PV14-56RX-C
Part Description	Ring Terminal, 16- 14 AWG, 5/16" stud size, vinyl insulated, expanded insulation for large wire O.D.
Product Type	Terminals
CSA Certified	Yes
UL Listed	Yes
Length (In.)	1.16
Length (mm)	29.5
Width (In.)	0.46
Width (mm)	11.7
CE Compliant	No
Clearance	0.37
Clearance (mm)	9.4
Insulation	Vinyl
Max. Ins.	0.200
Max. Ins. (mm)	5.1
Panduit Color Code	Blue
Plating Type	Tinned
Pricing Description	Ring Terminal, expanded vinyl insulation, 16 14 AWG, 5/16" stud size
Stock	0.03
Stock (mm)	0.8
Stud Hole Size (mm)	M8
Stud Size	5/16"
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)
Tool	CT-100A‡, CT-600-A‡, CT-1550‡, CT-1551‡, CT-2500‡
Wire Range	16 – 14 AWG
Wire Range (mm ²)	1.5 – 2.5
Min. Order UOM	PC
Min. Order Qty.	50
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.