

Search Results

Evaluate

- FAQ's
- Product Bulletins
- PDFObsolete and..
- Selection Guides
- PDFConvenience..

Design a Solution

- Part Drawings
- PDFRing Termina..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips


 Text Search: 'PV14-8R-E'

Your search criteria matched only one product, shown below

**PV14-8R-E**



- Insulation support helps to prevent wire damage in bending applications
  - Ring tongue design assures a secure connection in high vibration applications
  - Brazed seam protects terminal barrel from splitting during the crimp process
  - Internal barrel serrations assure good wire contact and maximum tensile strength
  - UL Flammability UL 94V -0, maximum insulation temperature 221°F (105°C)
  - UL and CSA rated up to 600 V per UL 486A/B, where applicable
  - ‡UL and CSA approved tooling/product combinations.
- Note: Wire sizes #26 – #22 AWG, are not UL Listed or CSA Certified.

Part Number	PV14-8R-E
RoHS Compliancy Status	Compliant
Part Description	Ring Terminal, 16- 14 AWG, #8 stud size, vinyl insulated, funnel entry.
Product Type	Terminals
CSA Certified	Yes
UL Listed	Yes
Length (In.)	0.92
Length (mm)	23.4
Width (In.)	0.31
Width (mm)	7.9
CE Compliant	No
Clearance	0.25
Clearance (mm)	6.4
Insulation	Vinyl
Max. Ins.	0.170
Max. Ins. (mm)	4.3
Panduit Color Code	Blue
Plating Type	Tinned
Pricing Description	Terminal Convenience Package
Stock	0.03
Stock (mm)	0.8
Stud Size	#8
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)
Tool	CT-100A‡, CT-600-A‡, CT-1550‡, CT-1551‡, CT-2500‡
Wire Range	16 – 14 AWG
Wire Range (mm²)	1.0 – 2.5
Min. Order UOM	PC
Min. Order Qty.	20
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.