


Model 5271 Extendible Tip Test Probe To Retractable Sheath Banana Plug Patch Cord



MATERIALS:

Extendible Tip Test Probe:

Extendible Tip: Stainless Steel.

Chuck: Brass, Electroless Nickel Plated.

Insulation: Tip – Kynar Shrink Tubing.

Probe Body and Chuck Nut – Nylon. Color Matches Color of Wire.

Wire:

18 AWG Stranding 65 x 36 t.c., PVC Insulated, .144 (3,66mm) O.D.

Marking: POMONA 5271-XX.

Color: Referenced by Part Number.

Retractable Sheath Banana Plug:

Banana Plug Spring: Beryllium Copper, Nickel Plated.

Plug Body: Brass, Nickel Plated.

Tip: Nylon. Color Matches Color of the Wire.

Compression Spring: Stainless Steel.

Insulation: Nylon Molded to the Plug Body and Wire. Color Matches Color of Wire.

RATINGS:

Operating Temperature: +80°C Max.

Operating Voltage: 1500 V AC/DC Max.

Current: 3 Amps Max.

ORDERING INFORMATION: 5271-XX-* XX = Wire Length, * = Color, -0 Black, -2 Red

Standard Lengths: 48" (121,92cm). Additional lengths can be quoted upon request. Ordering Example: 5271-12-0 Patch Cord is 12" (30,48cm), Color is Red.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA