

Search by SKU, Product Name or Keyword

**SEARCH**

**CART**



[Products](#) [Catalogs](#) [Free Samples](#) [Free CAD](#) [Knowledge Center](#) [Contact Us](#)

[Home](#) [Tooling & Positioning Comp...](#) [Locating & Positioning Com...](#) [Ball & Spring Plungers & Acc...](#) [Threaded Spring Plungers](#)



### 3/8-16 Steel Ball Spring Plunger

● In Stock

**Item Code:** ST-7

ST-7 features a 3/8-16 thread with a Steel Ball nose. The plunger has a body length of 1.130 in (28.7 mm) and an initial end force of 2.80 lbs (1.3 kg)



Description	Quantity	Options
<b>Nose Type</b> : Ball	<input type="text" value="1"/>	<div style="background-color: red; color: white; padding: 5px; text-align: center; margin-bottom: 5px;"><b>Add to Cart</b></div> <div style="background-color: #ccc; padding: 5px; text-align: center; margin-bottom: 5px;">Request CAD</div> <div style="background-color: #ccc; padding: 5px; text-align: center;">Request Quote</div>
<b>Body Material</b> : Steel		
<b>Nose Material</b> : Steel		
<b>Initial End Force</b> : 2.80 lbs (1.3 kg)		
<b>Thread Size</b> : 3/8-16		
<b>Body Length</b> : 1.130 in (28.7 mm)		
<b>Ball Diameter</b> : .186 in (4.7 mm)		
<b>Nose Projection</b> : .186 in (4.7 mm)		
<b>Special Features (All)</b> : No Locking Element		
<b>Finish</b> : Black Oxide		
<b>Brand</b> : Vliet		
<b>ID - Mfg Item Number</b> : S59		

[Print Page](#)

ESSENTIAL SOLUTIONS DELIVERED

- |  |   |  |  |
|--|---|--|--|
| <a href="#">Abrasives &amp; Grinding</a>           | <a href="#">Clamps &amp; Workholdings</a>           | <a href="#">Fiber, Wire &amp; Cable Management</a> | <a href="#">PCB &amp; Electronics Hardware</a>       |
| <a href="#">Access Hardware</a>                    | <a href="#">Cutting &amp; Machining</a>             | <a href="#">Flange Protection</a>                  | <a href="#">Pneumatics &amp; Hydraulics</a>          |
| <a href="#">Adhesives, Sealants &amp; Tapes</a>    | <a href="#">Extrusions &amp; Structural Systems</a> | <a href="#">Knobs, Handles &amp; Grips</a>         | <a href="#">Raw Materials</a>                        |
| <a href="#">Bearings &amp; Power Transmissions</a> | <a href="#">Fasteners</a>                           | <a href="#">Material Handling</a>                  | <a href="#">Tamper Evident &amp; Security Seals</a>  |
| <a href="#">Caps &amp; Plugs</a>                   | <a href="#">Feet, Casters &amp; Glides</a>          | <a href="#">Shop Supplies</a>                      | <a href="#">Tooling &amp; Positioning Components</a> |
|  |   |  | <a href="#">Tools &amp; Precision Instruments</a>    |



- |   |                                    |  |                                      |                               |
|---|------------------------------------|--|--------------------------------------|-------------------------------|
| <b>About Us</b>                           | <b>Customer Service</b>            | <b>Policies</b>                                  | <b>Terms of Use</b>                  | <b>ABOUT SSL CERTIFICATES</b> |
| <a href="#">About Essentra Components</a> | <a href="#">Contact Us</a>         | <a href="#">Privacy Policy</a>                   | <a href="#">Website Terms of Use</a> |                               |
| <a href="#">About Essentra PLC</a>        | <a href="#">Catalogs</a>           | <a href="#">Terms and Conditions of Sale</a>     | <a href="#">Cookie Policy</a>        |                               |
| <a href="#">Locations</a>                 | <a href="#">Sample Program</a>     | <a href="#">Terms and Conditions of Purchase</a> |                                      |                               |
| <a href="#">Knowledge Center</a>          | <a href="#">Free CAD</a>           | <a href="#">Environmental Policy</a>             |                                      |                               |
|   | <a href="#">Careers</a>            | <a href="#">Health and Safety</a>                |                                      |                               |
|   | <a href="#">Distributor Portal</a> | <a href="#">Quality Statement</a>                |                                      |                               |