



TE Connectivity: Every Connection Counts  
© 2017 TE Connectivity Ltd. family of companies. All Rights Reserved

**+** HARNESSING

CABLE-TO-CABLE SPLICING



✓ Active

TE CONNECTIVITY (TE)

D-200-0233-RT

Raychem | D-200

D-200-0233-RT

TE Internal Number: EG3678-000

Not Yet Reviewed for EU RoHS

Not Yet Reviewed for EU ELV

**Product Type** Cable Splice

**Number of Conductors** 2

**Cable Shield Plating Material** Nickel

**Side 1 Number of Cables Spliced** 2

**Shield Diameter (Max)** 6 mm [ .235 in ]

## DOCUMENTATION —

No documentation available.

## FEATURES +

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

**Product Type** Cable Splice

Configuration Features

**Number of Conductors** 2

## Body Features

**Cable Shield Plating Material** Nickel

**Side 1 Number of Cables Spliced** 2

**Side 2 Number of Cables Spliced** 2

**Crimp Style** Butt

**Cable Jacket Material** ETFE, Polyimide/PTFE

**Crimp Barrel Plating** Nickel

**Sealed** Yes

---

## Dimensions

**Shield Diameter (Max)** 6 mm [ .235 in ]

**Cable Insulation Diameter (Max)** 6.5 mm [ .255 in ]

**Cable Outside Diameter** 6.5 mm [ .255 in ]

**Wire Size (AWG)** 16 – 20

**Wire Outside Diameter** 2.8 mm [ .11 in ]

---

## Usage Conditions

**Operating Temperature (Max) (°C)** 200

**Operating Temperature Range (°C)** -65 – 200

**Cable Temperature Rating (°C)** 150

## Statement of Compliance

**Statement of Compliance**

PDF