


4

3

2

1

REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED
D	REV. PER ECN # T-8881	870930	I. MYON
E	REV. PER ECN # T-20028	95/9/19H-iggy	



TRIAx STRIP


(RAYTHEON #10270730)

TWINAX STRIP

(RAYTHEON # MIS-20054/1-001)

NOTES:

- PART DESCRIPTION: CONNECTOR, JACK, TRIAXIAL, BULKHEAD (RAYTHEON #1145047) COMPLETE WITH PREFLUXED SOLDER PREFORM RING AND HEAT SHRINKABLE INSULATING SLEEVE.
 - HOUSING ACCOMMODATION: HOUSING DESIGNED TO ACCEPT SHIELDED CONTACTS MIS-20067/1 THRU MIS-20067/4 SHIELDED; RAYCHEM SOLDER TACT D-602-44/45 AND D-602-54/55.
 - WIRE SIZE: HOUSING WILL TERMINATE OUTER SHIELD OF TRIAX/TWINAX CABLE HAVING A SHIELD DIAMETER OF .185 MAX.
 - MATING CONNECTOR: THIS CONNECTOR WILL MATE WITH D-621-0001 (RAYTHEON #11453046) CONNECTOR, PLUG SUBMINIATURE, TRIAXIAL.
- ITEMS SUPPLIED AS PART OF CONNECTOR ASSEMBLY.
- JAM NUT AND LOCKING WASHER SUPPLIED UNASSEMBLED.
- RECOMMENDED TWINAX STRIPING TOOL AD-1479 OR AD-1496
- SEE PROCEDURE ES 61124 FOR TERMINATION INFORMATION.
- MATERIAL: HOUSING BODY: BRASS ALLOY PER ASTM B16 (QQ-B-626)
JAM NUT: BRASS ALLOY PER ASTM B16 (QQ-B-626)
LOCK WASHER: STAINLESS STEEL PER QQ-S-763
INSULATING SLEEVE: HEAT SHRINKABLE, POLYVINYLDENE FLUORIDE (TRANSPARENT BLUE)
SOLDER RING: PREFLUXED SOLDER PREFORM, COMPOSITION Sn63, FLUX TYPE RMA, PER QQ-S-571
INSULATOR: THERMOPLASTIC PER LP 392
FINISH: HOUSING BODY: TIN PLATED PER MIL-T-10727
JAM NUT: NICKEL PLATED PER QQ-N-290
LOCK WASHER: PASSIVATE PER MIL-S-5002



If this document is printed it becomes uncontrolled.
Check with the web for latest revision.

ACCESSORIES	
CTA-0012	BARRIER TUBE
CTA-0013	PREFORM INSULATOR SLEEVES (2)
D-600-0024	STRAIN RELIEF

SPECIFICATION CONTROL DRAWING

© Raychem Corporation 1988

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. METRIC DIMENSIONS ARE IN BRACKETS.	DRAWN	CRN	76 10 19	Raychem RAYCHEM CORPORATION 300 CONSTITUTION DRIVE MILBURN PARK, CALIFORNIA 94025
	CHECKED	R. YATES	76 10 20	
	APPROVED	R. YATES	76 10 20	
	APPROVED			
DECIMALS	TITLE CONNECTOR, JACK, TRIAxIAL, BULKHEAD			
.XXX ± .005 [mm]				
.XX ± .01 [mm]				
ANGLES				
.X ±	CAD NAME			
WEIGHT	THIRD ANGLE PROJECTION			SIZE A CHG. ENT. NO. 08090 DRG. NO. D-621-0002 REV E DO NOT SCALE THIS DRAWING
lbs [g]				

1 ORIGINAL DOCUMENT

D-621-0002