

397945-000 Product Details



397945-000

TE Part Number: 397945-000

✓ Active

➤ [Add to Part List](#)

SolderShield Cable Splices

🌿 [Always ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Cable Type = Coaxial
- Number of Conductors = Single-conductor cable
- Wire Range = 1.25-3.00² [16-12] mm [AWG]
- Tin/Silver Conductor Plating
- Coaxial Cable Type = RG 178, RG 179, RG 187, RG 188, RG 196, RG 316, RG 404, RG M17/136-00001

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Documentation & Additional Information

Product Drawings:

- [Splice Coaxial Cable, Environment Resistant](#) (PDF, English)

Catalog Pages/Data Sheets:

- [Wire and Cable, Harnessing and Protection Products](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Product Images:

- [Product View](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Number of Conductors = Single-conductor cable
- Connection Type = Solder, Crimp

Body Related Features:

- Wire Range (mm [AWG]) = 1.25-3.00² [16-12]
- Conductor Plating = Tin/Silver

Configuration Related Features:

- [Cable Type](#) = Coaxial
- Coaxial Cable Type = RG 178, RG 179, RG 187, RG 188, RG 196, RG 316, RG 404, RG M17/136-00001

Industry Standards:

- [RoHS/ELV Compliance](#) = ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was ELV compliant

Conditions for Usage:

- Operating Temperature (Max.) (°C) = 150

Operation/Application:

- Application Type = Cable to cable splicing

Other:

- Brand = Raychem