



NT-1-0-SP Product Details

[Share](#) [Print](#) [Email](#)


NT-1-0-SP

TE Internal Number: 5550074007

[Active](#)

Heat Shrink Tubing

[Converted to EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Heat Shrinkable Tubing
- Product Name = NT
- Product Source = U.K., U.S.
- Flexible
- Medium Wall Style

[View all Features](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [Raychem NT Tubing Modified Chlorinated Polyolefin, E...](#) (PDF, English)

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Information](#)
- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Heat Shrinkable Tubing
- Material = Chlorinated Polyolefin
- Color = Black

Electrical Characteristics:

- Product Source = U.K., U.S.
- [Expanded ID, Min. \(mm \[in\]\)](#) = 25.40 [1.000]
- [Recovered ID, Max. \(mm \[in\]\)](#) = 14.50 [0.571]
- Product Use = Cables, Harnesses

Body Features:

- [Product Name](#) = NT
- Pliancy = Flexible
- [Wall Style](#) = Medium
- [Wall Type](#) = Single
- [Shrink Ratio](#) = 1.75:1
- Fluid Type = Brake Fluid, Chemicals/Solvents, Hydraulic Fluid, Lubricating Oil, Water
- Resistant To = Abrasion, Fluids, Strain
- Wall Thickness - Full Recovery (Nominal) (mm [in]) = 1.77 [0.070]

Housing Features:

- Material Systems = No
- Flammability Rating Type = Flame-Retardant

Industry Standards:

- Government/Industry Qualification = No
- UL Rating = Recognized
- CSA Certified = Yes
- Approved Standards = CSA LR31929, UL E35586
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

Environmental:

- Fluid Resistance = Splash Protection
- [Operating Temperature \(°C\)](#) = -70 - +121

Conditions for Usage:

- Full Recovery Temperature (°C) = 135
- Shrink Temperature, Min. (°C) = 90
- High Temperature Compatible = No

Operation/Application:

- Application = Cable Bundling, Cable Jacketing, Insulation and Protection
- Emission Free = No

Packaging Features:

- Packaging Method = Spool

Other:

- Brand = Raychem

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference Products](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

[▶](#)

