



D-110-20 Product Details

[Share](#) | [Print](#) | [Email](#)


Active

Solder Sleeve Wire Splices

D-110-20
D-110-20
 TE Internal Number: 625059-000

Product Highlights [View All](#)

- Wire Splice
- Splice Type = Solder Sleeve
- Fluid Resistance = Splash Protection
- Wire Temperature Rating Range (Max.) = 125°C
- Inside Diameter = 2.65 mm

[Pricing & Availability](#)
[Request Sample](#)
[Add to My Part List](#)
[Buy Product through Distributor](#)
[Feedback](#)
[Documents](#) | [Features](#) | [Compliance](#)

Please Note:
 Use the Product Drawing for all design activity

Product Type Features	
Product Type	Wire Splice
Splice Type	Solder Sleeve
Termination Features	
Connection Type	Solder
Dimensions	
Inside Diameter (mm [in])	2.65 [0.105]
Inside Diameter Fully Recovered (mm [in])	1.40 [0.055]
Length (mm [in])	13.30 [0.524]
Industry Standards	
RoHS/ELV Compliance	Not ELV/RoHS compliant
Lead Free Solder Processes	Not relevant for lead free process

Environmental	
Fluid Resistance	Splash Protection
Operating Temperature (Max.) (°C)	150
Conditions for Usage	
Wire Temperature Rating Range (Max.)	125°C
Operation/Application	
Application	Wire to Wire Splicing
Other	
Brand	Raychem
Node Classification	Splices

Related Products

Not quite the product you're looking for?
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed