




+ TERMINALS & SPLICES

SPLICES



✓ Active

TE CONNECTIVITY (TE)

D-436-42

Raychem

650072-000

TE Internal Number: 650072-000

Mil-Spec: M81824/9-2

Alias ID: 5-1195131-0

EU RoHS Compliant

EU ELV Compliant

Product Type Splice System Crimp

Terminal & Splice Style Splice

Wire Size (AWG) 24 – 20

Wire Size (mm²) .39 – 1.34

Barrel Inside Diameter 2.36 mm [.093 in]

 **PRODUCT DRAWING**
English

DOCUMENTATION

Product Drawings

In-Line Splice Sealing System, Multi-Wire

PDF

English

Catalog Pages/Data Sheets

1654025_Sec8_D-436

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Product Type Splice System Crimp

Splice Type Butt Splice

Body Features

Insulation Material Modified Polyvinylidene

Contact Features

Terminal & Splice Style Splice

Dimensions

Wire Size (AWG) 24 – 20

Wire Size (mm²) .39 – 1.34

Barrel Inside Diameter 2.36 mm [.093 in]

Wire Size (CMA) 779 – 2680

Usage Conditions

Operating Temperature Range (°C) 150

Industry Standards

Government Qualified No

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
