



[+ TERMINALS & SPLICES](#)

SPLICES



✓ Active

TE CONNECTIVITY (TE)
D-436-0128

Raychem

650110-000

TE Internal Number: 650110-000

Alias ID: 5-1195132-7

[EU RoHS Compliant](#)

[EU ELV Compliant](#)

Product Type Splice System Crimp

Terminal & Splice Style Splice

Wire Size (mm²) .15 – .75

Wire Size (CMA) 304 – 1510

Splice Type Parallel Splice

[↓ PRODUCT DRAWING](#)
English

DOCUMENTATION

Product Drawings

Stub Splice Sealing System, Tin Plated Crimp

PDF

English

Catalog Pages/Data Sheets

1654025_Sec8_D-436

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Product Type Splice System Crimp

Splice Type Parallel Splice

Body Features

Insulation Material Modified Polyvinylidene

Contact Features

Terminal & Splice Style Splice

Dimensions

Wire Size (mm²) .15 – .75

Wire Size (CMA) 304 – 1510

Usage Conditions

Operating Temperature Range (°C) 150

Industry Standards

Government Qualified No

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
