



+ TERMINALS & SPLICES

SPLICES



✓ Active

TE CONNECTIVITY (TE)

D-436-87

Raychem

650131-000

TE Internal Number: 650131-000

Mil-Spec: M81824/8-3

Alias ID: 2-1195133-1

Not Yet Reviewed for EU RoHS

Not Yet Reviewed for EU ELV

Product Type Splice System Crimp

Terminal & Splice Style Splice

Wire Size (mm²) .95 – 3.37

Barrel Inside Diameter 4.06 mm [.16 in]

Wire Size (CMA) 1900 – 6755

↓ **PRODUCT DRAWING**
English

DOCUMENTATION

Product Drawings

Low Outgassing In-Line Splice Sealing System, 2 Or 3 To 1 Splicer: Nickel Plated, Color Coded, With Inspection Slots

PDF

English

Catalog Pages/Data Sheets

1654025_Sec8_D-436

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Product Type Splice System Crimp

Splice Type Butt Splice

Body Features

Insulation Material Modified Polyvinylidene

Contact Features

Terminal & Splice Style Splice

Dimensions

Wire Size (mm²) .95 – 3.37

Barrel Inside Diameter 4.06 mm [.16 in]

Wire Size (CMA) 1900 – 6755

Usage Conditions

Operating Temperature Range (°C) 150

Industry Standards

Government Qualified No

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
