



Accessories - Cable Clamp Fitting (Low Profile) Fits Metric & PG Threads



Part Numbers	Cable Range	Thread Type & Size See page 49 for thread specs	Dimensions in Inches (mm)			
			A Hole O.D.	H Body Length	T Thread Length	F Wrench Flat
 Nickel Plated Brass						
KL12MA-BR	.20 - .30 (5-7.5)	M12 x 1.5	.47 (12)	.59 (15)	.22 (5.5)	.63 (16)
KL16MA-BR	.28 - .39 (7-10)	M16 x 1.5	.63 (16)	.63 (16)	.24 (6)	.75 (19)
KL20MA-BR	.39 - .55 (10-14)	M20 x 1.5	.79 (20)	.71 (18)	.26 (6.5)	.94 (24)
KL25MA-BR	.47 - .85 (12-21.5)	M25 x 1.5	.98 (25)	.83 (21)	.31 (8)	1.34 (34)
KL32MA-BR	.63 - 1.06 (16-27)	M32 x 1.5	1.26 (32)	.87 (22)	.31 (8)	1.65 (42)
KL40MA-BR	.87 - 1.30 (22-33)	M40 x 1.5	1.57 (40)	1.00 (25.5)	.37 (9.5)	2.05 (52)
KL50MA-BR	.98 - 1.52 (25-38.5)	M50 x 1.5	1.97 (50)	1.00 (25.5)	.37 (9.5)	2.05 (52)




This clamp offers **Extra Pull-out Resistance**. Made of durable Nickel Plated Brass, it offers an excellent solution for your specific application needs. Not a liquid tight solution.


Also available in PG Threads!

Accessories - Deep Socket Wrenches for Strain Relief Fittings - Nickel Plated Brass

Part Numbers	Used with Sizes		Dimensions in Inches (mm)			
	Nylon Dome Nut See page 49 for thread specs	Brass Dome Nut See page 49 for thread specs	F Wrench Flat	L Length	C Inner Diameter	D Outer Diameter
S-1400-WR		PG7, M12	.55 (14)	2.36 (60)	.35 (9)	.75 (19)
S-1500-WR	PG7, M12		.59 (15)	2.36 (60)	.37 (9.5)	.79 (20)
S-1700-WR		PG 9, 3/8" NPT, M16	.67 (17)	2.36 (60)	.39 (10)	.93 (23.5)
S-1900-WR	PG 9, 3/8" NPT, M16	3/8" NPT, M16	.75 (19)	2.36 (60)	.43 (11)	1.02 (26)
S-2000-WR		PG 11, M16-E	.79 (20)	2.36 (60)	.47 (12)	1.06 (27)
S-2200-WR	PG 11, 3/8" NPT, M16-E	PG 13 / 13.5, 1/2" NPT, M20	.87 (22)	2.36 (60)	.51 (13)	1.16 (29.5)
S-2400-WR	PG 13 / 13.5, 1/2" NPT, M20	PG 16, 1/2" NPT-E, M20-E	.94 (24)	2.36 (60)	.59 (15)	1.28 (32.5)
S-2700-WR	PG 16, 1/2" NPT-E, M20-E		1.06 (27)	2.36 (60)	.67 (17)	1.40 (35.5)
S-3000-WR		PG 21, 3/4" NPT, M25	1.18 (30)	2.36 (60)	.71 (18)	1.59 (40.5)
S-3300-WR	PG 21, 3/4" NPT, M25		1.30 (33)	2.36 (60)	.79 (20)	1.71 (43.5)
S-3600-WR	PG 21		1.42 (36)	2.36 (60)	.87 (22)	1.87 (47.5)
S-4000-WR		PG 29, 1" NPT, M32	1.57 (40)	3.94 (100)	.98 (25)	2.07 (52.5)
S-4100-WR	PG 29		1.61 (41)	3.94 (100)	1.06 (27)	2.11 (53.5)
S-4200-WR	PG 29, 1", 1-1/4" NPT, M32		1.65 (42)	3.94 (100)	1.06 (27)	2.15 (54.5)
S-4600-WR	1-1/4" NPT		1.81 (46)	3.94 (100)	1.22 (31)	2.36 (60)
S-5000-WR		PG 36, M40	1.97 (50)	3.94 (100)	1.26 (32)	2.58 (65.5)
S-5300-WR	PG 36, 1-1/2" NPT, M40		2.09 (53)	3.94 (100)	1.26 (32)	2.82 (71.5)
S-5500-WR	M 50	M 50	2.17 (55)	3.94 (100)	1.26 (32)	2.83 (72)
S-5700-WR		PG 42, M50	2.24 (57)	3.94 (100)	1.42 (36)	2.97 (75.5)
S-6000-WR	PG 42, M50		2.36 (60)	3.94 (100)	1.50 (38)	3.09 (78.5)
S-6400-WR		PG 48, M63	2.52 (64)	3.94 (100)	1.57 (40)	3.31 (84)
S-6500-WR	PG 48, M63		2.56 (65)	3.94 (100)	1.65 (42)	3.35 (85)
S-6800-WR	M63	M63	2.68 (68)	3.94 (100)	1.65 (42)	3.43 (87)



The handy, light weight **Deep Socket Wrench** is manufactured from alloy steel. It is slit open along the full length to accommodate the installed cable during tightening of the dome nut. The wrench encloses the dome nut on five sides, giving the nut additional rigidity during tightening. This is especially important if a stiff cable is used. Does not work with all Flex Fittings.



For Material Specifications and Approval Information, please refer to page 45.