




**STL - Stand-Off Twist Lock**


**4/2011-2**




**PRODUCT DATA:**

Material: UL94 V-2 Nylon 6/6 RMS-01 Color: Natural	Material: UL94 V-0 Nylon 6/6 RMS-19 Color: Natural	"A"	"B" REF.	BUNDLE Ø		
STL-J#-250-4M-01	STL-J#-250-4M-19	4	19.1	5.1-7.65		
STL #-250-3-01	STL #-250-3-19	4.8				
STL-J#-250-6M-01	STL-J#-250-6M-19	6				
STL-J#-250-8M-01	STL-J#-250-8M-19	8				
STL-J#-250-10M-01	STL-J#-250-10M-19	10				
STL-J#-250-12M-01	STL-J#-250-12M-01	12				
STL #-250-8-01	STL #-250-8-19	12.7				
STL #-250-12-01	STL #-250-12-19	19.1				
STL #-250-16-01	STL #-250-16-19	25.4				
STL #-250-20-01	STL #-250-20-19	31.8				
STL-J#-350-4M-01	STL-J#-350-4M-19	4			23.1	7.6-10.2
STL #-350-3-01	STL #-350-3-19	4.8				
STL-J#-350-6M-01	STL-J#-350-6M-19	6				
STL-J#-350-8M-01	STL-J#-350-8M-19	8				
STL-J#-350-10M-01	STL-J#-350-10M-19	10				
STL-J#-350-12M-01	STL-J#-350-12M-19	12				
STL #-350-8-01	STL #-350-8-19	12.7				
STL #-350-12-01	STL #-350-12-19	19.1				
STL #-350-16-01	STL #-350-16-19	25.4				
STL #-350-20-01	STL #-350-20-19	31.8				
STL-J#-450-4M-01	STL-J#-450-4M-19	4	27.7	10.2-12.7		
STL #-450-3-01	STL #-450-3-19	4.8				
STL-J#-450-6M-01	STL-J#-450-6M-19	6				
STL-J#-450-8M-01	STL-J#-450-8M-19	8				
STL-J#-450-10M-01	STL-J#-450-10M-19	10				
STL-J#-450-12M-01	STL-J#-450-12M-19	12				
STL #-450-8-01	STL #-450-8-19	12.7				
STL #-450-12-01	STL #-450-12-19	19.1				
STL #-450-16-01	STL #-450-16-19	25.4				
STL #-450-20-01	STL #-450-20-19	31.8				
STL-J#-600-4M-01	STL-J#-600-4M-19	4			32.5	12.7-15.2
STL #-600-3-01	STL #-600-3-19	4.8				
STL-J#-600-6M-01	STL-J#-600-6M-19	6				
STL-J#-600-8M-01	STL-J#-600-8M-19	8				
STL-J#-600-10M-01	STL-J#-600-10M-19	10				
STL-J#-600-12M-01	STL-J#-600-12M-19	12				
STL #-600-8-01	STL #-600-8-19	12.7				
STL #-600-12-01	STL #-600-12-19	19.1				
STL #-600-16-01	STL #-600-16-19	25.4				
STL #-600-20-01	STL #-600-20-19	31.8				
STL-J#-750-4M-01	STL-J#-750-4M-19	4	36.8	17.8-20.3		
STL #-750-3-01	STL #-750-3-19	4.8				
STL-J#-750-6M-01	STL-J#-750-6M-19	6				
STL-J#-750-8M-01	STL-J#-750-8M-19	8				
STL-J#-750-10M-01	STL-J#-750-10M-19	10				
STL-J#-750-12M-01	STL-J#-750-12M-19	12				
STL #-750-8-01	STL #-750-8-19	12.7				
STL #-750-12-01	STL #-750-12-19	19.1				
STL #-750-16-01	STL #-750-16-19	25.4				
STL #-750-20-01	STL #-750-20-19	31.8				


Replace # with Fix style required. Example: STL-J1-250-4M-01




Standard fix (delete the # in the part number)




Bottom Hole: Snap-lock Ø 4.75 ± 0.08  
Panel Thickness: 0.8-2




Bottom Hole: Snap-lock Ø 4 ± 0.08  
Panel Thickness: 0.8-2




Bottom Hole: Snap-lock 5.5 square  
Panel Thickness: 0.8-2




Bottom Hole: Press-fit Ø 7.9 ± 0.08  
Panel Thickness: 6.4 min.





Bottom Hole: Snap-lock Ø 6.5 ± 0.09  
Panel Thickness: 0.8-1.6



Bottom Hole: Snap-lock Ø 6 ± 0.08  
Panel Thickness: 0.78-2



Bottom Hole: See panel detail Fix.7  
Panel Thickness: 0.8-1.6



Bottom Hole: See panel detail Fix.9  
Panel Thickness: 0.8-1.6

