

**Cookies on  
EssentraComponentsUS**

Cookies are used on this website to give you the best experience possible.  
By continuing to use this site you are agreeing to our [Cookie Policy](#)

**x Hide**



Contact Us: 800-847-0486

United States English

**Login or Register**

**ESSENTRA**  
COMPONENTS

Search

**CART**

**Products      Contact Us      Order Catalog**

[Home](#)    [PCB & Electronics Hardware](#)    [Fan Hardware](#)    [Fan Mounts](#)



## Fan Mount - Elastomer,.984 in Min Fan Thk,40 Shore A

In Stock !

**Item Code:** FM-7

Free sample available

This product has a high elongation rubber for easy fan mounting and component assembly and provides shock and vibration protection. It is Style 3 made of 40 Shore A Silicone Rubber



Description		<p style="text-align: center;"><b>Add to Cart</b></p> <div style="text-align: center;"> <input type="button" value="Request CAD"/>    <input type="button" value="Order Sample"/>    <input type="button" value="Request Quote"/> </div>
<b>Style</b>	: 3	
<b>Full Material</b>	: Silicone Rubber	
<b>Color</b>	: Black	
<b>Hardness</b>	: 40 Shore A	
<b>Head Diameter</b>	: 8.0 mm (0.315 in)	
<b>Hole Diameter</b>	: 3.5 mm (0.138 in)	
<b>Minimum Fan Thickness</b>	: 25.0 mm (0.984 in)	
<b>Maximum Fan Thickness</b>	: 28.0 mm (1.102 in)	
<b>Overall Length</b>	: 73.0 mm (2.874 in)	
<b>Operating Temperature Range</b>	: -40 - 302 °F (-40 - 150 °C)	
<b>Material Type</b>	: RMS-316	
<b>Material</b>	: Rubber	
<b>Type</b>	: One End - Flexible	
<b>Fan Thickness Range</b>	: 25.0 - 28.0 mm (1.102 in)	

[Downloads](#)

[Print Page](#)