

Search by SKU, Product Name or Keyword

SEARCH

CART



[Products](#) [Catalogs](#) [Free Samples](#) [Free CAD](#) [Knowledge Center](#) [Contact Us](#)

[Home](#) [Caps, Plugs & Masking](#) [Push Fit Caps](#) [Tube Caps & Bar Caps](#) [Round End Caps](#)



Vinyl Round End Cap: .156 in (4 mm) ID, .500 in (12.7 mm) Inside Height, 350 °F (176.7 °C) Max. Temp.

● In Stock

Item Code: DM0156-1/2A

PVC Push Fit Vinyl Round End Cap has an I. D. of .156 in (4 mm) that can stretch onto larger dimensions for a snug fit. The Black glossy finish is attractive as a decorative end cap.

Description	Quantity	Options
Inside Diameter : .156 in (4 mm) Inside Height : .500 in (12.7 mm) Color : Black Material : PVC Fitting Style : Push Fit Full Material : Polyvinyl Chloride Temperature Range : 350 °F (176.7 °C)	<input type="text" value="1"/> <div style="background-color: red; color: white; padding: 5px; text-align: center; margin: 5px 0;">Add to Cart</div> <div style="background-color: #ccc; padding: 5px; text-align: center; margin: 5px 0;">Request CAD</div> <div style="background-color: #ccc; padding: 5px; text-align: center; margin: 5px 0;">Free Sample</div> <div style="background-color: #ccc; padding: 5px; text-align: center; margin: 5px 0;">Request Quote</div>	



Print Page

Recently Viewed



Vinyl Round End Cap:
.156 in (4 mm) ID, .500
in (12.7 mm) Inside
Height, 350 °F
(176.7 °C) Max.
Temp.

ESSENTIAL SOLUTIONS

DELIVERED

[Abrasives & Grinding](#)
[Access Hardware](#)
[Adhesives, Sealants & Tapes](#)
[Bearings & Power Transmissions](#)
[Caps & Plugs](#)

[Clamps & Workholdings](#)
[Cutting & Machining](#)
[Extrusions & Structural Systems](#)
[Fasteners](#)
[Feet, Casters & Glides](#)

[Fiber, Wire & Cable Management](#)
[Flange Protection](#)
[Knobs, Handles & Grips](#)
[Material Handling](#)
[Shop Supplies](#)

[PCB & Electronics Hardware](#)
[Pneumatics & Hydraulics](#)
[Raw Materials](#)
[Tamper Evident & Security Seals](#)
[Tooling & Positioning Components](#)
[Tools & Precision Instruments](#)



[About Essentra Components](#)
[About Essentra PLC](#)
[Locations](#)
[Knowledge Center](#)

[Contact Us](#)
[Catalogs](#)
[Sample Program](#)
[Free CAD](#)
[Careers](#)
[Distributor Portal](#)

[Privacy Policy](#)
[Terms and Conditions of Sale](#)
[Terms and Conditions of](#)
[Purchase](#)
[Environmental Policy](#)
[Health and Safety](#)
[Quality Statement](#)

[Website Terms of Use](#)
[Cookie Policy](#)

ABOUT SSL CERTIFICATES