

Product type designation

Product description

PROFIBUS FC bus connector RS 485

Bus connector with axial cable outlet (180°)
 PROFIBUS FC RS 485 plug 180 PROFIBUS connector with
 FastConnect connection plug and axial cable outlet for Industry PC,
 SIMATIC OP, OLM, Transfer rate: 12 Mbit/s, terminating resistor with
 isolating function, Plastic enclosure



Suitability for use

For connecting PROFIBUS nodes to the PROFIBUS bus cable

Transmission rate

Transfer rate / with PROFIBUS

9.6 kbit/s ... 12 Mbit/s

Interfaces

Number of electrical connections

- for PROFIBUS cables
- for network components or terminal equipment

2

1

Type of electrical connection

- for PROFIBUS cables
- for network components or terminal equipment

Integrated insulation displacement contacts for 2-core PB FC
 installation cables

Sub-D connector (9-pin)

Type of electrical connection / FastConnect

Yes

Mechanical data

Design of terminating resistor

Integrated resistor combination that can be selected with slide
 switch. Disconnect function: When the resistor is connected, the
 outgoing bus is isolated.

Material / of the enclosure

plastic

Locking mechanism design	Screw
--------------------------	-------

Design, dimensions and weight

Type of cable outlet	180° cable outlet
Width	16 mm
Height	62 mm
Depth	34.5 mm
Net weight	40 g

Permitted ambient conditions

Ambient temperature	
<ul style="list-style-type: none"> during operation 	-40 ... +70 °C
<ul style="list-style-type: none"> during storage 	-25 ... +80 °C
<ul style="list-style-type: none"> during transport 	-25 ... +80 °C
Relative humidity / at 25 °C / without condensation / during operation / maximum	75 %
Protection class IP	IP20

Product properties, functions, components / general

Product feature	
<ul style="list-style-type: none"> silicon-free 	Yes
Product component	
<ul style="list-style-type: none"> PG connection socket 	No
<ul style="list-style-type: none"> strain relief 	Yes

Standards, specifications, approvals

Certificate of suitability	
<ul style="list-style-type: none"> RoHS conformity 	Yes
<ul style="list-style-type: none"> UL approval 	Yes
<ul style="list-style-type: none"> cULus approval 	Yes
<ul style="list-style-type: none"> Railway application in accordance with EN 50155 	No

Further Information / Internet Links

Internet-Link	
<ul style="list-style-type: none"> to website: Selector SIMATIC NET SELECTION TOOL 	http://www.siemens.com/snst
<ul style="list-style-type: none"> to website: Industrial communication 	http://www.siemens.com/simatic-net
<ul style="list-style-type: none"> to website: Industry Mall 	https://mall.industry.siemens.com
<ul style="list-style-type: none"> to website: Information and Download Center 	http://www.siemens.com/industry/infocenter
<ul style="list-style-type: none"> to website: Image database 	http://automation.siemens.com/bilddb
<ul style="list-style-type: none"> to website: CAx Download Manager 	http://www.siemens.com/cax
<ul style="list-style-type: none"> to website: Industry Online Support 	https://support.industry.siemens.com

last modified: 01/10/2019