

RF 19 H, gold, full illumination, 2.9^{±0.6} N, lamp white, bezel white, 1



fields of application

- > Measurement-control-regulation
- > Mechanical and system engineering
- > Automotive
- > Electro-medical

special features

- ➤ Gold contacts, reliable switching with low currents
- > Full illumination
- > Min. key grid 24 mm
- > Overall height: 12.5 mm
- > Terminal technology: THT

$c \in$

description

The RF 19 H gold tactile switches have a 19 x 19 mm edge length, reliable gold contacts and a noticeable click. They are used in flat data entry keyboards under overlays or under keycaps, such as RAFI RK 90 keycaps.

Flat data entry keyboards with RF 19 H elements should be constructed in a 24 mm grid. With this grid, strips of glue remain between the individual keys on the front panel. The overlay, which we recommend embossing above the key switches, can be glued onto these strips of glue.

The key switch can be locked with an O-ring (accessory) and used as a signal indicator or placeholder.

technical data

| > general | | |
|--|--------------------------|-----------------|
| illuminated | Yes | direct links |
| Bezel color | white | > RAFI eCatalog |
| Luminous element color | white | |
| Operating temperature, min. | -25 °C | |
| Operating temperature, max. | 70 °C | |
| Storage temperature, min. | -25 °C | |
| Storage temperature, max. | 70 °C | |
| Luminous elements | Full illumination 2 LEDs | |
| Soldering time for manual soldering, max. | 5 sec | |
| Soldering temperature for manual soldering | 350 °C | |
| Soldering temperature for wave soldering | 260 °C | |
| Soldering | Manual / wave | |

The information in this data sheet only contains general descriptions and / or performance features, which may not apply precisely as described to the respective application, and which my change due to further product enhancements. The technical data, illustrations and other information about our products are the mere results of individual technical testing. These descriptions and other product features are only binding if they expressly agreed upon at the time of the conclusion of a binding contract. In all other cases, we reserve the right to make technical changes as well as changes of availability. Pictures and other graphic illustrations are approximations only. All product names may be trademarks or brand names of the RAFI Group or any other sub-supplier of RAFI. The use of such by any third parties for their own purposes may infringe the rights of the respective entity holding those rights.

RAFI GmbH & Co. KG

Ravensburger Str. 128-134 88276 Berg / Ravensburg Germany www.rafi.de, info@rafi.de

3.14.002.684/0000



Solder heat resistance according DIN EN 60068-2-20

to standard

Packaging Tube
Packaging unit 25 pcs.

Environment resistance IEC 60068-2-14

IEC 60068-2-30 IEC 60068-2-33 IEC 60068-2-78 1,000,000 Cycles

RoHS compliant Yes

REACH compliant Yes

> mounting diameters

Operating life

Installation height 12.5 mm

Grid, min. 24 mm

Outside dimension, length 19.05 mm

Outside dimension, width 19.05 mm

Outside dimension, height 12.5 mm

> mechanical data

Actuation function momentary contact function

Operating force, max. 100 N
Operating force, min. $2.9^{\pm0.6}$ N
Switching travel $0.5^{+0.2}$ mm

Contact function 1 NO

Contact system Snap-action contact

Contact material Gold

Fixing Soldering

Terminal on the rear THT

Lötbarkeit Yes

> electrical data

Operating voltage of the luminous 24 V

element, max.

Rated voltage, min.

Rated voltage, max.

Rated current, min.

Rated current, max.

0.1 A

Rated power, max.


2 W

3.14.002.684/0000




drawings

Dimensioned drawing




light field 16 x 16

front panel drawing



Circuit diagram



Button full illumination