

PFV 系列
SERIES

UPGRADE

贴片型 125°C 4000小时品 (混合型)
Load Life : 125°C 4000 hours (Hybrid Type), Chip Type

- 高耐压(~63Vdc)、超低ESR品、高纹波品、小型化品
High Voltage(~63Vdc), Ultra Low ESR, High Ripple Current, Miniaturized.
- 可对应AEC-Q200。
AEC-Q200.

RoHS
compliance

◆规格表／SPECIFICATIONS

| 项目 Items | 特性 Characteristics | | | | | | | | | |
|--|---|--|----------------------------|---|---------------------------|--|---------------|--|----------------------|---|
| 工作温度范围 Category Temperature Range | -55~+125°C | | | | | | | | | |
| 额定电压范围 Rated Voltage Range | 25~63Vdc | | | | | | | | | |
| 静电容量允许差 Capacitance Tolerance | ±20% (20°C, 120Hz) | | | | | | | | | |
| 漏电电流 Leakage Current(MAX) | 标准品一览表如下 (施加额定电压2分钟后) The value is shown in "STANDARD SIZE" table (After 2 minutes) | | | | | | | | | |
| 损失角正切值(tan δ) Dissipation Factor(MAX) | 标准品一览表如下 (20°C, 120Hz) The value is shown in "STANDARD SIZE" table (20°C, 120Hz) | | | | | | | | | |
| 耐久性 Endurance | 在125°C环境中, 不超过额定电压的范围内叠加额定纹波电流, 连续加载4000小时后, 满足以下各项。 After applying rated voltage with rated ripple current for 4000 hours at 125°C, the capacitors shall meet the following requirements. <table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <td style="padding: 2px;">静电容量变化率 Capacitance Change</td> <td style="padding: 2px;">初期值的±30%以内 Within ±30% of the initial value.</td> </tr> <tr> <td style="padding: 2px;">损失角正切值 Dissipation Factor</td> <td style="padding: 2px;">初期规格值的200%以下 Not more than 200% of the initial specified value.</td> </tr> <tr> <td style="padding: 2px;">等效串联电阻 E.S.R.</td> <td style="padding: 2px;">初期规格值的200%以下 Not more than 200% of the initial specified value.</td> </tr> <tr> <td style="padding: 2px;">漏电电流 Leakage Current</td> <td style="padding: 2px;">初期规格值以下 Not more than the initial specified value.</td> </tr> </table> | | 静电容量变化率 Capacitance Change | 初期值的±30%以内 Within ±30% of the initial value. | 损失角正切值 Dissipation Factor | 初期规格值的200%以下 Not more than 200% of the initial specified value. | 等效串联电阻 E.S.R. | 初期规格值的200%以下 Not more than 200% of the initial specified value. | 漏电电流 Leakage Current | 初期规格值以下 Not more than the initial specified value. |
| 静电容量变化率 Capacitance Change | 初期值的±30%以内 Within ±30% of the initial value. | | | | | | | | | |
| 损失角正切值 Dissipation Factor | 初期规格值的200%以下 Not more than 200% of the initial specified value. | | | | | | | | | |
| 等效串联电阻 E.S.R. | 初期规格值的200%以下 Not more than 200% of the initial specified value. | | | | | | | | | |
| 漏电电流 Leakage Current | 初期规格值以下 Not more than the initial specified value. | | | | | | | | | |
| 高温高湿负荷 Biased Humidity | 在85°C、85%RH中, 施加额定电压2000小时后、满足下记各项。 After applying rated voltage for 2000 hours at 85°C and humidity of 85%, the capacitors shall meet the following requirements. <table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <td style="padding: 2px;">静电容量变化率 Capacitance Change</td> <td style="padding: 2px;">初期值的±30%以内 Within ±30% of the initial value.</td> </tr> <tr> <td style="padding: 2px;">损失角正切值 Dissipation Factor</td> <td style="padding: 2px;">初期规格值的200%以下 Not more than 200% of the initial specified value.</td> </tr> <tr> <td style="padding: 2px;">等效串联电阻 E.S.R.</td> <td style="padding: 2px;">初期规格值的200%以下 Not more than 200% of the initial specified value.</td> </tr> <tr> <td style="padding: 2px;">漏电电流 Leakage Current</td> <td style="padding: 2px;">初期规格值以下 Not more than the initial specified value.</td> </tr> </table> | | 静电容量变化率 Capacitance Change | 初期值的±30%以内 Within ±30% of the initial value. | 损失角正切值 Dissipation Factor | 初期规格值的200%以下 Not more than 200% of the initial specified value. | 等效串联电阻 E.S.R. | 初期规格值的200%以下 Not more than 200% of the initial specified value. | 漏电电流 Leakage Current | 初期规格值以下 Not more than the initial specified value. |
| 静电容量变化率 Capacitance Change | 初期值的±30%以内 Within ±30% of the initial value. | | | | | | | | | |
| 损失角正切值 Dissipation Factor | 初期规格值的200%以下 Not more than 200% of the initial specified value. | | | | | | | | | |
| 等效串联电阻 E.S.R. | 初期规格值的200%以下 Not more than 200% of the initial specified value. | | | | | | | | | |
| 漏电电流 Leakage Current | 初期规格值以下 Not more than the initial specified value. | | | | | | | | | |
| 低温特性 Low Temperature Characteristics (阻抗比) Impedance Ratio(MAX) | $Z(-55^\circ\text{C})/Z(+20^\circ\text{C}) \leq 2.0$ (100kHz) $Z(-25^\circ\text{C})/Z(+20^\circ\text{C}) \leq 1.5$ | | | | | | | | | |

◆产品型号体系／PART NUMBER


| | | | | | |
|-----------------------|----------------|---------------------|----------------------------------|---------------|-------------------|
| □□□ | PFV | □□□□□ | M | □□□ | DXL |
| 额定电压 Rated Voltage | 系列名称 Series | 静电容量 Capacitance | 静电容量允许差 Capacitance Tolerance | 副记号 Option | 铝壳尺寸 Case Size |

◆纹波电流补正系数／

MULTIPLIER FOR RIPPLE CURRENT

| | | | | |
|---------------------|------|------|------|-------|
| 频率(Hz) Frequency | 120 | 1k | 10k | 100k≤ |
| 系数 Coefficient | 0.05 | 0.30 | 0.70 | 1.00 |

◆标识／MARKING




※电压记号 Voltage code

| | | | | |
|----------------------------|----|----|----|----|
| 额定电压(Vdc) Rated Voltage | 25 | 35 | 50 | 63 |
| 额定电压记号 Voltage code | E | V | H | J |

◆尺寸图／DIMENSIONS

(mm)



| ϕD | L | A1 | B1 | C | W1 | P |
|----------|------|------|------|-----|---------|-----|
| 6.3 | 6.1 | 6.6 | 6.6 | 2.7 | 0.5~0.8 | 1.8 |
| 6.3 | 8 | 6.6 | 6.6 | 2.7 | 0.5~0.8 | 1.8 |
| 8 | 10.5 | 8.3 | 8.3 | 2.9 | 0.8~1.1 | 3.1 |
| 10 | 10.5 | 10.3 | 10.3 | 3.2 | 0.8~1.1 | 4.5 |

※关于 $\phi 8$ 、 $\phi 10$ 也可对应耐振规格。详情,请参阅贴片型铝电解电容器的带辅助端子的耐振构造品项目。
Vibration proof package is also available for $\phi 8$ and $\phi 10$. For details, please refer to chip aluminum electrolytic capacitors section .

◆标准品一览表／STANDARD SIZE

| 额定电压 Rated Voltage (Vdc) | 静电容量 Capacitance (μF) | 外形尺寸 Size $\phi D \times L$ (mm) | 损失角正切值 (tan δ) (120Hz, 20°C) | 漏电流 Leakage Current ($\mu A/2min$) | 等效串联电阻 E.S.R.(m Ω ,max) | | 额定纹波电流 Rated Ripple Current (mA r.m.s./125°C, 10kHz) |
|--------------------------------|------------------------------------|--|--|--|-----------------------------------|--------------|--|
| | | | | | 20°C, 100kHz | -40°C, 10kHz | |
| 25 | 56 | 6.3×6.1 | 0.14 | 14.0 | 50 | 75 | 900 |
| | 100 | 6.3×8 | 0.14 | 25.0 | 30 | 45 | 1400 |
| | 220 | 8×10.5 | 0.14 | 55.0 | 27 | 41 | 1600 |
| | 330 | 10×10.5 | 0.14 | 82.5 | 20 | 30 | 2000 |
| 35 | 47 | 6.3×6.1 | 0.12 | 16.4 | 60 | 90 | 900 |
| | 68 | 6.3×8 | 0.12 | 23.8 | 35 | 53 | 1400 |
| | 150 | 8×10.5 | 0.12 | 52.5 | 27 | 41 | 1600 |
| | 270 | 10×10.5 | 0.12 | 94.5 | 20 | 30 | 2000 |
| 50 | 22 | 6.3×6.1 | 0.10 | 11.0 | 80 | 120 | 750 |
| | 33 | 6.3×8 | 0.10 | 16.5 | 40 | 60 | 1100 |
| | 68 | 8×10.5 | 0.10 | 34.0 | 30 | 45 | 1250 |
| | 100 | 10×10.5 | 0.10 | 50.0 | 28 | 42 | 1600 |
| 63 | 10 | 6.3×6.1 | 0.08 | 6.3 | 120 | 180 | 700 |
| | 22 | 6.3×8 | 0.08 | 13.8 | 80 | 120 | 900 |
| | 33 | 8×10.5 | 0.08 | 20.8 | 40 | 60 | 1100 |
| | 56 | 10×10.5 | 0.08 | 35.3 | 30 | 45 | 1400 |