Heavy Duty Fuse Clip, 10.3 x 38 /10.3 x 85 mm, 1500 VAC/VDC, 32 A





Heavy duty fuse clip Solder THT terminal

Heavy duty fuse clip Screw or rivet terminal

1500 V · 32 A

Description

- Solder, screw or rivet mounting
- For photovoltaic and other DC applications
- Suitable gPV fuse link ASO 10.3x38

Unique Selling Proposition

- Unique 1500 VDC/VAC and 32 A
- Minimal power loss due to strong clamping force

See below:

Approvals and Compliances

Applications

- All photovoltaic applications
- Inverters
- Battery charge controllers
- String fuse holder
- DC applications

References

Fuseholder to AEO 10.3x38; ASO 10.3x38

Weblinks

pdf data sheet, html datasheet, General Product Information, Packaging details, Distributor-Stock-Check, Accessories, Detailed request for product. Microsite

Tech	nical	Data

Fuse-Link	10.3 x 38 / 10.3 x 85 mm
Mounting	PCB
Terminal	Solder THT, screw or rivet
Rated Voltage	1500 V
Rated current	32A
Admissible Ambient Air Temp.	-40°C to 155°C 1)
Climatic Category	40/155/21 acc. to IEC 60068-1 1)
Material	Copper alloy, silver-plated / tin-plated 1)
Storage Conditions	0°C to 60°C, max. 70% r.h.
Product Marking	5 , Type

Soldering Methods	Wave
	Soldering Profile
Solderability	245°C / 3 sec acc. to IEC 60068-2-20,
	Test Ta, method 1
Resistance to Soldering Heat	260°C / 10 sec acc. to IEC 60068-2-20,
	Test Tb, method 1
Contact Resistance	≤ 1 mΩ at 100 mA
	-

Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in Details about Approvals

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

Approvals

The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products. Approval Reference Type: CSO

Approval Logo Certificates **Certification Body** Description

UL Approvals Ш Ul File Number: F39328 دار کی الک

¹⁾ Details see table of variants

Product standards

Product standards that are referenced

Organization Design Standard Description	Organization	Design	Standard	Description
--	--------------	--------	----------	-------------

(Jr)

Designed according to UL 4248-1

Fuseholder general requirements



Designed according to CSA C22.2 no. 4248.1

Fuseholder general requirements

Application standards

Application standards where the product can be used

Organization Design Standard Description

IEC

Designed for applications acc. IEC/UL 60950

Description

"REACH") entered into force.

IEC 60950-1 includes the basic requirements for the safety of information

 $technology\ equipment.$

Compliances

The product complies with following Guide Lines

Identification	Details	Initiator	Description
C€	CE declaration of conformity	SCHURTER AG	The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008.
ROHS	RoHS	SCHURTER AG	Directive RoHS 2011/65/EU, Amendment (EU) 2015/863
©	China RoHS	SCHURTER AG	The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.
REACH	REACH	SCHURTER AG	On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration,


Dimension [mm]

12 mm









Solder THT version

Drilling diagram









Screw or rivet version

Drilling diagram



All Variants

Weight	Terminal	Packaging	Admissible Ambient Air Temp.	Climatic Category	Coating	Order Number
4.45 g	Screw or Rivet	Bulk 128 x 91 x 60 mm (100 pcs.)	-40°C - 155°C	40/155/21	silver-plated	0751.0500
4.45 g	Screw or Rivet	Bulk 251 x 159 x 152 mm (1000 pcs.)	-40°C - 155°C	40/155/21	silver-plated	0751.0501
4.45 g	Screw or Rivet	Bulk 128 x 91 x 60 mm (100 pcs.)	-40°C - 125°C	40/125/21	Tin-plated	0751.0502
4.45 g	Screw or Rivet	Bulk 251 x 159 x 152 mm (1000 pcs.)	-40°C - 125°C	40/125/21	Tin-plated	0751.0503
4.6 g	Solder, THT	Bulk 128 x 91 x 60 mm (100 pcs.)	-40°C - 155°C	40/155/21	silver-plated	0751.0505
4.6 g	Solder, THT	Bulk 251 x 159 x 152 mm (1000 pcs.)	-40°C - 155°C	40/155/21	silver-plated	0751.0506
4.6 g	Solder, THT	Bulk 128 x 91 x 60 mm (100 pcs.)	-40°C - 125°C	40/125/21	Tin-plated	0751.0507
4.6 g	Solder, THT	Bulk 251 x 159 x 152 mm (1000 pcs.)	-40°C - 125°C	40/125/21	Tin-plated	0751.0508

Most Popular.

Availability for all products can be searched real-time:https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER

Accessories

Description



ESO 10.3x38 Fuse Inserter/Extractor with Cover Function for $10.3x38 \ mm$ Fuses in Clips, Patent Pending