

LV HRC fuse element, NH000, In: 2 A, gG, Un AC: 690 V, Un DC: 250 V, Front indicator, live grip lugs



Model	
product brand name	SENTRON
product designation	LV HRC fuse link
design of the product	With blade contacts
design of an identification indicator	Front indicators
design of the switching contact	Non-corroding, silver-plated
design of the fuse link	LV HRC fuse link
General technical data	
size of fuse system / acc. to DIN EN 60269-1	NH000
operating class of the fuse link	gG
circuit-breaker / Design	3NA3
type of voltage	AC/DC
operating current / at AC / rated value	2 A
supply voltage	
• at AC / rated value	690 V
• at DC	250 V
Protection class	
protection class IP	IP20, with connected conductors

Switching capacity

switching capacity current

- at DC / acc. to IEC 60947-2 / rated value 25 kA
- acc. to IEC 60947-2 / rated value 120 kA

Dissipation

power loss [W] 1.57 W

power loss [W] / for rated value of the current / at AC / in hot operating state / per pole 1.57 W

Current

Tripping residual / rated value / derated current / at 40 Cel 1.9 A

Diken-export / Let-through energy DE_3NA_00_690_gG_2

Mechanical Design

width

- of the enclosure 21 mm

mounting position Any, preferably vertical

net weight 128 g

Environmental conditions

ambient temperature

- minimum -5 °C
- maximum 40 °C




ambient temperature / during storage Air humidity 90% at 20 °C


environmental category -20 to +50 at 95% relative humidity

Certificates

reference code

- acc. to DIN EN 61346-2 F
- acc. to DIN EN 81346-2 F

General Product Approval	Declaration of Conformity	Test Certificates
 CCC	 VDE	 EG-Konf.
		Special Test Certificate
		Type Test Certificates/Test Report
		Miscellaneous

Shipping Approval	other
 GL	Environmental Conformations
	Miscellaneous

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NA3802-6>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NA3802-6>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NA3802-6

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



1

-F1



2

