

3RF2050-1AA45



Semiconductor relay, 1-phase 3RF2 Overall width 45 mm, 50 A 48-600 V / 4-30 V DC screw terminal Blocking voltage 1200 V

- List Price > Show prices
- Customer Price > Show prices
- DataSheet in PDF Download
- Service & Support (Manuals, Certificates, FAQs...) ↗ Download

> Image gallery and data for M-CAD and E-CAD (6) (6)

| Product  |   |
|--|---|
| Article Number (Market Facing Number)                                    | 3RF2050-1AA45   |
| Product Description  | Semiconductor relay, 1-phase 3RF2 Overall width 45 mm, 50 A 48-600 V / 4-30 V DC screw terminal Blocking voltage 1200 V |
| Product family   | > SIRIUS 3RF2 solid-state relays and solid-state contactors   |
| Product Lifecycle (PLM)  | PM300:Active Product  |
| Price data   |   |
| Price Group  | 41C   |
| List Price   | > Show prices   |
| Customer Price   | > Show prices   |
| Surcharge for Raw Materials  | None  |
| Metal Factor   | None  |
| Delivery information   |   |
| Export Control Regulations   | AL : N / ECCN : EAR99   |
| Standard lead time ex-works  | 5 Day/Days  |
| Net Weight (kg)  | 0,085 Kg  |
| Packaging Dimension  | 49,00 x 64,00 x 76,00   |
| Package size unit of measure   | MM  |
| Quantity Unit  | 1 Piece   |
| Packaging Quantity   | 1   |
| Additional Product Information   |   |
| EAN  | 4011209652569   |
| UPC  | 754554925790  |
| Commodity Code   | 85364900  |
| LKZ_FDB/ CatalogID   | CC-IC10   |
| Product Group  | 3725  |
| Group Code   | R711  |
| Country of origin  | Germany   |
| Compliance with the substance restrictions according to RoHS directive   | Since: 28.05.2009   |
| Product class  | C: products manufactured / produced to order, which cannot be reused or re-utilised or be returned against credit.      |
| WEEE (2012/19/EU) Take-Back Obligation                                   | Yes   |
| REACH Art. 33 Duty to inform according to the current list of candidates | ▶ Lead CAS-No. 7439-92-1 > 0, 1 % (w / w)   |

| Classifications |         |                |  |
|-----------------|---------|----------------|--|
|                 | Version | Classification |  |
| eClass          | 6       | 27-37-10-14    |  |
| eClass          | 7.1     | 27-37-10-14    |  |
| eClass          | 8       | 27-37-10-14    |  |
| eClass          | 9       | 27-37-10-14    |  |
| eClass          | 9.1     | 27-37-10-14    |  |
| ETIM            | 6       | EC002055       |  |
| ETIM            | 7       | EC002055       |  |
| IDEA            | 4       | 4755           |  |
| UNSPSC          | 14      | 39-12-23-33    |  |
| UNSPSC          | 15      | 39-12-15-29    |  |