



Representative



Line Art

**Catalog Number:** B87G  
**Product ID:** 7TAI029630R0049  
**UPC Number:** 78621080913  
**Status:** A

Brazed Seam Uninsulated Ring Terminal For Wire Range 16-14 AWG, Stud Size #10, Metallic

- These ring terminals are made of electrolytic copper for high conductivity.
- They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire).
- Serrated barrel
- Application Tools: WT110M, WT111M, WT112M, WT2000, ERG4002

### North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Type	Non-Insulated Ring Terminal
Special Features	These ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire). Serrated barrel increases grip on wire.
Standard	UL E9809
Wire Size	16-14 AWG
Voltage Rating	600 V
Material	Copper
Color	Metallic

### European Specifications (ETIM)

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	None
Reel packaging	N
AWG-range	16-14

### Packaging

Inner Quantity	1000
Inner Dimensions (inches)	4.3x3.3x4.3
Outer Quantity	10000
Outer Dimensions (inches)	12x10x8
Weight Uom	0.63 lbs. per 1000

**For further technical assistance, please contact us...**

ABB Installation Products - USA  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120  
 www.tnb.com

ABB Installation Products Technical Support  
 MS 3B-50  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: techsupport@tnb.com