



Representative

Catalog Number: G2-12
Product ID: 7TAI029580R0034
UPC Number: 78621087195
EAN Number: 05414363151630
Status: A

Non-Insulated Tubular Ring Terminal, Length 1.79 Inches, Width .80 Inches, Bolt Hole 1/2 Inch, Wire Range 2/2AN, Copper, Tin Plated

- These non-insulated ring terminals are made of electrolytic copper for high conductivity.
- They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire).
- Application Tools: WT115A, TBM6, TBM6S, WT3185

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Non-Insulated Ring Terminal
Special Features	These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire).
Standard	UL E9809
Wire Size	2 AWG
Voltage Rating	600 V
Material	Copper
Color	Metallic

European Specifications (ETIM)

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	Straight
Slender flange model	N
Insulated	N
With sight-hole	Y
Material	Copper
Surface protection	Tinned
Number of fixing holes	1

Packaging

Inner Quantity	10
Inner Dimensions (inches)	2.09x1.1x2.9
Outer Quantity	100
Outer Dimensions (inches)	10.3x8.6x7.1
Weight Uom	3.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000219
--------------------------------	------------

For further technical assistance, please contact us...

ABB Installation Products - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com