



Actual

Catalog Number: H973
Product ID: 7TAI029610R0014
UPC Number: 78621081520
EAN Number: 05415022255270
Status: A

Non-Insulated Tubular Ring Terminal, Length 1.65 Inches, Width .77 Inches, Bolt Hole 3/8 Inch, Wire Range 1AN-1/0, Copper, Tin Plated, 100 Pack

- These non-insulated ring terminals are made of electrolytic copper for high conductivity.
- They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire).
- Application Tools: TBM6, TBM6S, WT3185

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Type	Non-Insulated Ring Terminal
Special Features	These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire).
Standard	UL E9809
Wire Size	1AN-1/0
Voltage Rating	600 V
Material	Copper
Color	Metallic

European Specifications (ETIM)

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	Straight
Slender flange model	N
Insulated	N
With sight-hole	Y
Material	Copper
Surface protection	Tinned
Number of fixing holes	1

Packaging

Inner Quantity	100
Inner Dimensions (inches)	5x4.5x3
Outer Quantity	1000
Outer Dimensions (inches)	24x10.7x3.5
Weight Uom	5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000219
Catalog Page	Available on Website

For further technical assistance, please contact us...

ABB Installation Products Canada
 700, Thomas Avenue
 Saint-Jean-sur-Richelieu, QC
 J2X 2M9
www.tnb.ca

ABB Installation Products Technical Support
<http://www.tnb.ca/en/contactus/?id=ALL>

Hours: 7h00 - 18h00
 Monday-Friday