



Actual

Location: Mandeville

SCHELL/MARTIN

414 N CAUSEWAY BLVD
STE A

Catalog Number: L-11-40-9-D
Product ID: 7TAG054250R0006
UPC Number: 72849493304
EAN Number: 05414363132844
Status: A

Intermediate Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 299mm (11.77 Inches), Width of 3.6mm (0.14 Inches), Thickness of 1.25mm (0.049 Inches), Bundle Diameter 2mm (0.08 Inches) to 76mm (2.99 Inches), Tensile Strength Rating of 178 Newtons (40 Pounds), Bulk Pack

- Application Tools: ERG50, QC-100, L-200, L-400-C

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Brand Name	Catamount
Type	Intermediate
Standard	UL E49405
Width	0.14 in ; 3.6 mm
Length	11.77 in ; 299 mm
Thickness	0.049 in ; 1.25 mm
Bundle Diameter	0.08 to 2.99 in ; 2 to 76 mm
Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Plastic Pawl
Tensile Strength	40 pounds ; 178 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	3.6mm
Length belt/tape/tie	299mm
Tie thickness	1.25mm
Max. bundle diameter	76mm
Min. holding force	178N
Operating temperature	-40-+85°C
Model	Internal toothing
Band closure	Plastic lip/-cam
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
Halogen free	Y
Colour	Natural colour
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N

Packaging

Inner Quantity	500
Inner Dimensions (inches)	14.5x10.05x2.5
Outer Quantity	5000
Outer Dimensions (inches)	16.6x13.2x10.9
Weight Uom	3 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000221
--------------------------------	------------

For further technical assistance, please contact us...

ABB Installation Products - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com