## Cost optimized pulse transformers for THT mounting



## See below:

# **Approvals and Compliances**

## Description

- High insulation rating (>2.2 kVAC) between the primary and the secondary windings
- Small coupling capacitances between primary and secondary windings limit transient feedback from the power supply side to the control electronics
- Cost optimized design
- The defined partial discharge voltage guarantees an effecively unlimited serviceable live

#### **Applications**

- Galvanic separation of drive- and power-circuit
- Mainly used in ignition circuits with Thyristors, Triacs, power transistors and IGBT's
- DC/DC Converters
- Line coupling transformers in high speed data transmission

#### Weblinks

pdf data sheet, html datasheet, General Product Information, Approvals, Distributor-Stock-Check, Detailed request for product

<b>Technical Dat</b>
----------------------

Rated voltage	up to 500 VAC
Voltage Time Integral	200 - 500 Vμs
Pulse Rise Time	0.5 - 1.5µs
Turns Ratio	1:1, 1:1:1, 3:1:1
Terminal Type	THT
Weight	7 - 15g
Material: Housing	UL 94V-0
Sealing Compound	UL 94V-0
	-

Climatic Category	25/100/21 acc. to IEC 60068-1
Allowable Operation Temp.	-25°C to 70°C

## **Approvals and Compliances**

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in Details about Approvals

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

# **Application standards**

Application standards where the product can be used

Organization	Design	Standard	Description
<u>IEC</u>	Designed for applications acc.	IEC/UL 62368-1	IEC 62368-1 includes the basic requirements for safety of audio, video, information technology and office equipment.


# Compliances

The product complies with following Guide Lines

Identification	Details	Initiator	Description
ROHS	RoHS	SCHURTER AG	Directive RoHS 2011/65/EU, Amendment (EU) 2015/863
<b>©</b>	China RoHS	SCHURTER AG	The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.
REACH	REACH	SCHURTER AG	On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.


# Dimension [mm]

Case 14-8




1) Prim.


Case 05-7



Case 14-9



Case 05-8



1) Prim.

# **All Variants**

1) Prim.

_	Order Number	Housings	Packing unit [pcs.]	Weight [g]	P <sub>m</sub> [W]	C <sub>C</sub> [pF]	R <sub>S</sub> [Ω]	<b>R</b> <sub>P</sub> [Ω]	L <sub>s</sub> [mH]	U <sub>s</sub> x T <sub>w</sub> [Vµs]	U <sub>isol</sub> [kV]	U <sub>VAC</sub> [V]	I <sub>ign</sub> [A]	T <sub>r</sub> [µs]	Turns Ratio
	IL-11-0001	05-7	50	7 g	0.5	10	1.2	1.2	8.0	500	3.5	500	0.1	1	1:1
	IL-11-0002	05-7	50	7 g	0.5	8	0.6	0.6	2.5	250	3.5	500	0.25	1	1:1
	IL-21-0001	14-9	50	15 g	1.1	8	0.6	0.6	3.0	300	4.0	380	0.25	1	1:1
	IL-10-0001	05-8	50	7 g	0.5	10	0.6	0.6	2.5	250	3.5	380	0.1	0.5	1:1:1
	IL-10-0003	05-8	50	7 g	0.5	8	0.4	0.4	1.5	200	3.5	380	0.25	1	1:1:1
	IL-20-0001	14-8	50	15 g	1.1	8	0.6	0.6	3.0	300	4.0	380	0.25	1.5	1:1:1
	IL-10-0002	05-8	50	7 g	0.5	10	0.5	2.3	16.5	200	3.5	380	0.1	0.7	3:1:1

Most Popular.