

Axial Lead Fuse, 6.3x32 mm, 440 - 500 VAC, 400 - 500 VDC, 1-8 A, High Breaking Capacity  $\geq 1500$  A

new



UL 248-14 · 440 - 500 VAC · Quick-Acting F

See below:

[Approvals and Compliances](#)

### Description

- 6.3 x 32 mm fuses for primary protection
- 10 rated currents from 1 A to 8 A

### Unique Selling Proposition

- High rated voltages up to 500 VAC / DC
- High breaking capacity  $\geq 1500$  A

### Applications

- 3-phase applications
- DC applications
- Power supplies
- Frequency converter
- Power electronics


### References

[Packaging Details](#)

### Weblinks

[pdf data sheet](#), [html datasheet](#), [General Product Information](#), [Packaging details](#), [Distributor-Stock-Check](#), [Detailed request for product](#)

### Technical Data

|                              |  |
|------------------------------|--|
| Rated Voltage                | 440 - 500 VAC, 63 - 500 VDC  |
| Rated current                | 1 - 8 A  |
| Breaking Capacity            | 1500 A - 20 kA   |
| Characteristic               | Quick-Acting F   |
| Mounting                     | Solder, THT  |
| Admissible Ambient Air Temp. | -40 °C to 85 °C  |
| Climatic Category            | 40/085/21 acc. to IEC 60068-1  |
| Material: Tube               | Ceramics   |
| Material: Endcaps            | Nickel-Plated Copper Alloy   |
| Material: Axial Leads        | Tin-Plated Copper  |
| Unit Weight                  | 3.54 g   |
| Storage Conditions           | 0 °C to 60 °C, max. 70% r.h.   |
| Product Marking              |  Type, Rated current, Rated Voltage, Characteristic, Breaking capacity, Approvals |

|                              |  |
|------------------------------|--|
| Solderability                | 235 °C / 2 sec acc. to IEC 60068-2-20  |
| Resistance to Soldering Heat | 260 °C / 10 sec acc. to IEC 60068-2-58 |

### Approvals and Compliances


Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in [Details about Approvals](#)

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

### Approvals



The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products.

Approval Reference Type: SHF 6.3x32 Pigta

| Approval Logo   | Certificates                 | Certification Body | Description            |
|---|------------------------------|--------------------|------------------------|
|  | <a href="#">UL Approvals</a> | UL                 | UL File Number: E41599 |


## Product standards

Product standards that are referenced

| Organization   | Design                | Standard           | Description                                     |
|--|-----------------------|--------------------|---|
|  | Designed according to | UL 248-14          | Low voltage fuses - Part 14: Additional fuses   |
|  | Designed according to | CSA22.2 No. 248.14 | Low-Voltage Fuses - Part 14: Supplemental Fuses |





## Application standards

Application standards where the product can be used


| Organization   | Design                         | Standard       | Description  |
|--|--------------------------------|----------------|--|
|  | Designed for applications acc. | IEC/UL 62368-1 | IEC 62368-1 includes the basic requirements for safety of audio, video, information technology and office equipment. |


## Compliances

The product complies with following Guide Lines

| Identification   | Details                                      | Initiator   | Description   |
|--|--|-------------|---|
|  | <a href="#">CE declaration of conformity</a> | SCHURTER AG | The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008. |
|  | RoHS   | SCHURTER AG | Directive RoHS 2011/65/EU, Amendment (EU) 2015/863  |
|  | China RoHS                                   | SCHURTER AG | The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.  |
|  | REACH  | SCHURTER AG | On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.                               |

## Dimension [mm]

 6.3 mm




ØA = 0.8 mm

## Pre-Arcing Time

| Rated Current In | 1.5 x In min. | 2.1 x In max. | 2.75 x In min. | 2.75 x In max. | 4.0 x In min. | 4.0 x In max. | 10.0 x In min. | 10.0 x In max. |
|------------------|---------------|---------------|----------------|----------------|---------------|---------------|----------------|----------------|
| 1 A - 1 A        | 60 min        | 30 min        | 20 ms          | 1.5 s          | 8 ms          | 400 ms        | -              | 20 ms          |
| 1.25 A - 8 A     | 60 min        | 30 min        | 100 ms         | 5 s            | 20 ms         | 1 s           | -              | 50 ms          |

Time-Current-Curves



All Variants

| Rated Current [A] | Rated Voltage [VAC] | Rated Voltage [VDC] | Breaking Capacity | Voltage Drop 1.0 I <sub>n</sub> max. [mV] | Power Dissipation 1.5 I <sub>n</sub> max. [mW] | Melting I <sup>2</sup> t 10.0 I <sub>n</sub> typ. [A <sup>2</sup> s] | Order Number |
|-------------------|---------------------|---------------------|-------------------|---|--|--|--------------|
| 1                 | 500                 | 500                 | 1)                | 400                                       | 1200   | 1.5 ●  | 8020.5068.PT |
| 1.25              | 500                 | 500                 | 1)                | 300                                       | 1300   | 2.9 ●  | 8020.5069.PT |
| 1.6               | 500                 | 400                 | 2)                | 300                                       | 1400   | 5.8 ●  | 8020.5070.PT |
| 2                 | 500                 | 400                 | 2)                | 280                                       | 1700   | 2 ●  | 8020.5071.PT |
| 2.5               | 500                 | 400                 | 2)                | 260                                       | 2000   | 3.8 ●  | 8020.5072.PT |
| 3.15              | 500                 | 400                 | 2)                | 240                                       | 2300   | 8.6 ●  | 8020.5073.PT |
| 4                 | 500                 | 400                 | 2)                | 220                                       | 2900   | 14.6 ●   | 8020.5074.PT |
| 5                 | 500                 | 400                 | 2)                | 190                                       | 2900   | 33.2 ●   | 8020.5075.PT |
| 6.3               | 500                 | 400                 | 2)                | 170                                       | 3400   | 61.6 ●   | 8020.5076.PT |
| 8                 | 500                 | 400                 | 2)                | 160                                       | 3700   | 120 ●  | 8020.5077.PT |

Availability for all products can be searched real-time: <https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

- 1) 1500 A @ 500 VAC, cos φ = 0.99 - 1  
 1500 A @ 250 VAC, cos φ = 0.7 - 0.8  
 10 kA @ 125 VAC, cos φ = 0.7 - 0.8  
 1500 A @ 500 VDC  
 20 kA @ 63 VDC
- 2) 1500 A @ 500 VAC, cos φ = 0.99 - 1  
 1500 A @ 250 VAC, cos φ = 0.7 - 0.8  
 10 kA @ 125 VAC, cos φ = 0.7 - 0.8  
 1500 A @ 400 VDC  
 20 kA @ 63 VDC

Packaging Unit Bulk (100 pcs.)