

REV. Status

ISSUE 1
4/28/92 YN

ISSUE 2
REFORMATTED
TEMECULA
WAS CARSON
9/13/95 DS

1. Electrical specifications

- 1.1 Input voltage: AC 120V ±10% 60 Hz ±0.5 Hz
- 1.2 Output voltage and current: AC 22V at 900mA

V _{in}	900mA Load	90mA Load
108	18.1 VAC MIN	-
120	20.6-23.0 VAC	25.6 VAC MAX
132	-	28.4 VAC MAX


NOTE: Specification applies after 10 minutes warm-up with 900mA load and at any operating temperature

- 1.3 Operating temperature: 0 ° C to +40 ° C
- 1.4 Storage temperature: -20 ° C to +85 ° C
- 1.5 Operating and Storage Humidity: 0 to 95% without condensation
- 1.6 Withstand voltage: AC 1500Vrms 1 minute @ input to output
- 1.7 Input earth prong is connected to output "G" terminal


2. Typical performance data test condition: Ta = +25° C, measured after 10 minute warm-up with input at 120V 60Hz

3. Safety agencies
UL File No. E82180
CSA File No. LR38236

4. Nameplate: See drawing P-N1-11160 for detail



5. Mechanical Specifications;
All dimensions shown are nominal unless otherwise specified



PREPARED BY:

K. Brennan
ENGINEER:

D. Suzuki
QUALITY CONTROL:

V. Casey

APPROVED:

O. Vulf

DWG CONTROL NO.
P-A7-10678
ACAD\PS\A7106781.DWG

REV
A

UL/CSA AC 22V 900mA
POWER SUPPLY

830A0066-03

MODEL SPECIFICATION

CONTENTS OF THIS DRAWING ARE
SUBJECT TO CHANGE WITHOUT
PRIOR NOTICE

TAMURA CORPORATION OF AMERICA
43352 BUSINESS PARK DRIVE, TEMECULA, CA. 92590-6624
(909) 699-1270 FAX 9096769482

DIM: mm(In) SCL: NONE SH: 1 OF 1

PROPRIETARY NOTICE: THIS DRAWING PRINT OR DOCUMENT AND SUBJECT MATTER DISCLOSED HEREIN ARE PROPRIETARY ITEMS TO WHICH TAMURA RETAINS THE EXCLUSIVE RIGHT OF DISSEMINATION, REPRODUCTION, MANUFACTURE AND SALE. THIS DRAWING, PRINT OR DOCUMENT IS SUBMITTED IN CONFIDENCE FOR CONSIDERATION BY THE RECIPIENT ALONE UNLESS PERMISSION FOR FURTHER DISCLOSURE IS EXPRESSLY GRANTED IN WRITING.