Status REVISION -04/06/98 TS

> REVISION A ADDED RoHS 12/02/05 MP


AUDIO COUPLING MINIATURE ENCAPSULATED TRANSFORMER DESIGNED TO OPERATE 10mW MAX IN PRIMARY AND REFLECT A PRIMARY SOURCE IMPEDANCE OF APPROXIMATELY 100KΩCT WITH 1.0KΩCT LOAD ON SECONDARY.

- A. Electrical Specifications (@ 20°C)
 - 1. Pri Source Impedance; 100KΩ CT
 - 2. Sec Load Impedance; $1.0 \text{K}\Omega$ CT
 - 3. Pri DC Current; 0mA MAX
 - 4. Operating Level; 10mW MAX @ 300Hz
 - 5. Frequency Response (relative to 1KHz); ±2.0dB, @ 300Hz to 100KHz
 - 6. Longitudinal Balance: 60dB MIN @ 1KHz
 - 7. DC Resistance;

1-3) 4300 Ω ±30% (4-6) 120Ω ±20%

- 8. Turns Ratio; (1-3): (4-6) = 10.0 : 1 ±2%
- 9. Dielectric Strength;

500 Vrms 0.5 minute @ Pri - Sec



TOLERANCES (mm) 4 ± 0.2 $4 \le 20 \pm 0.3$ $20 \le 50 \pm 0.4$

PREPARED BY:

K. BRENNAN

ENGINEER: M. PITCHAI QUALITY CONTROL:

T. CLEM

CONTENTS OF THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT PRIOR NOTICE

P-A1-12000

ACAD\MET\A1120001.DWG

CONTROL NO. REV

 $2.50\pm0.25(0.10\pm0.01)$ TYP -

AUDIO COUPLING MINIATURE ENCAPSULATED TRANSFORMER

TAMURA CORPORATION OF AMERICA

43352 BUSINESS PARK DRIVE, TEMECULA, CA. 92590-6624 (951) 699-1270 FAX 9516769482

−10.4(0.41)MAX

MET-02 MODEL SPECIFICATION

DIM: mm(In) SCL: 2/1 SH: 1 0F

APPROVED: PROPRIETARY NOTICE: THIS DRAWING PRINT OR DOCUMENT AND SUBJECT MATTER DISCLOSED HEREIN ARE PROPRIETARY ITEMS TO WHICH TAMURA RETAINS THE EXCLUSIVE RIGHT OF DISSEMINATION, REPRODUCTION, MANUFACTURE AND SALE. THIS DRAWING, PRINT OR DOCUMENT IS SUBMITTED IN CONFIDENCE FOR CONSIDERATION BY THE RECIPIENT ALONE UNLESS PERMISSION FOR FURTHER DISCLOSURE IS EXPRESSLY GRANTED IN WRITING. Y. SEKIGUCHI