

Isopropyl Alcohol (IPA) Wipes – 70%

Product# 1608-100DSP, 1608-100FL, 1608-100R

Product Description

Convenient, low linting wipes are pre-saturated with 70% pure IPA. 3 choices packaging choices available:

- Flip-top tubs - Spring-loaded lid automatically closes and sealed top reduces waste from dry-out
- Disposable tubs - Lower cost disposable tub
- Refill rolls - Replacement wipes fit in either Flip-top or Pop-up tubs to save money and reduce waste

Features / Benefits

- 70% IPA & 30% DI water
- 5"x8" (127mm x 203mm) wipes
- 100 wipes/tub
- Lint-free, tear resistant polyester

Environmental Policy

Techspray® is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

Resources

Techspray® products are supported by global sales, technical and customer services resources.

For additional technical information on this product or other Techspray® products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at: www.techspray.com.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray® be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.



Typical Product Data and Physical Properties

Specific Gravity:	0.81
Solubility in Water:	Soluble
Evaporation rate:	<1 (Ether = 1)
Flash Point (TCC):	61°F/16°C
Percent Volatile:	100%
Shelf life:	2 years

Material Specifications

1608-100DSP/ -100FL/ -100R fill	336 grams
1608-100DSP/ -100FL/ -100R wipe size	7-3/4" x 5-1/4"

Packaging and Availability

1608-100FL (Flip-top tub)	100ct (5"x8" wipe size)
1608-100DSP (Pop-up tub)	100ct (5"x8" wipe size)
1608-100R (refill)	100ct (5"x8" wipe size)