



RVS-13(B5) Product Details

[Share](#) | [Print](#) | [Email](#)


RVS-13(B5)

TE Internal Number: 135603-000

 [Active](#)

Power Cable Splices, Repair Sleeves and End Seals

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Jacket Sealing Kit
- Splice Style = In-Line
- RVS Series
- Above Ground Application, Direct Burial Application, Submersible Application
- Cable Type = Polymeric

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Jacket Sealing Kit
- Splice Style = In-Line
- Series = RVS
- Cable Type = Polymeric
- Number of Conductors = 1
- Jacketed Cable = With
- Package = 5 kits/box

Mechanical Attachment:

- Retention Type = Adhesive Only

Body Features:

- Cable Outer Diameter (mm [in]) = 18.00 - 30.00 [0.700 - 1.200]
- Connector Length, Max (mm [in]) = 178 [7]
- Sleeve Length, Nominal (mm [in]) = 305 [12]

Configuration Features:

- Conductor (Wire) Size = 250 - 600 kcmil
- Cable Shielding = With

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Printer/Label Features:

- Voltage Rating (kV) = 1

Operation/Application:

- Application = Above Ground, Direct Burial, Submersible
- Cable Shield Style = JCN

Other:

- Installation Type = Cold Applied
- Brand = Raychem

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

[▶](#)

