



Actual

Catalog Number: L-11-50-9-D
Product ID: 7TAG054330R0005
UPC Number: 72849491130
EAN Number: 05414363132882
Status: Active

Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 295.66mm (11.64 Inches), Width of 4.73mm (0.186 Inches), Thickness of 1.35mm (0.053 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds), Bulk Pack

- Application Tools: ERG50, QC-100, L-200, L-400-C

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Brand Name	Catamount
Type	Standard
Standard	UL E49405
Width	0.186 Inch/4.73mm
Length	11.64 Inches/295.66mm
Thickness	0.053 Inch/1.35mm
Bundle Diameter	0.0625 Inches/1.59mm-3.0 Inches/76.2mm
Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Plastic Pawl
Tensile Strength	50 Pounds/220 Newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	4.73mm
Length belt/tape/tie	295.66mm
Tie thickness	1.35mm
Min. holding force	222N
Model	Internal toothing
Band closure	Plastic lip/-cam
Material	Plastic
Material quality	Polyamide PA
Halogen free	Y
Colour	Natural colour
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N

Packaging

Inner Quantity	500
Inner Dimensions (inches)	17x12x3
Outer Quantity	5000
Outer Dimensions (inches)	17.1x13.2x10.6
Weight Uom	4.38 lbs. per 1000

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000222

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com