



Representative

Catalog Number: BC87
Product ID: 7TAI029630R0057
UPC Number: 78621088032
Status: A

Non-Insulated Heavy Duty Ring Terminal, Length .87 Inches, Width .39 Inches, Bolt Hole #10, Wire Range #16-#14 AWG Heavy Duty, Copper, Tin Plated, 500 Pack

- These non-insulated ring terminals are made of electrolytic copper for high conductivity.
- They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire).
- Serrated barrel increases grip on wire.
- Application Tools: WT110M, WT111M, WT112M, WT2000, ERG4002
- Alternate Package Qty: BC14-10

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Type	Non-Insulated Heavy-Duty Ring Terminal
Special Features	These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire). Serrated barrel increases grip on wire.
Standard	UL E9809
Wire Size	16-14 AWG
Voltage Rating	600 V
Material	Copper
Color	Metallic

European Specifications (ETIM)

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	None
Reel packaging	N
AWG-range	16-14
Material	Copper
Surface protection	Tinned

Packaging

Inner Quantity	500
Inner Dimensions (inches)	4x4x3
Outer Quantity	5000
Outer Dimensions (inches)	5.2x4.5x3.1
Weight Uom	6.25 lbs. per 1000

Documents / Support Tools

Catalog Page	Available on Website
--------------	----------------------

For further technical assistance, please contact us...

ABB Installation Products Canada
 700, Thomas Avenue
 Saint-Jean-sur-Richelieu, QC
 J2X 2M9
www.tnb.ca

ABB Installation Products Technical Support
<http://www.tnb.ca/en/contactus/?id=ALL>

Hours: 7h00 - 18h00
 Monday-Friday