



Representative

**Catalog Number:** G971  
**Product ID:** 7TAI029610R0009  
**UPC Number:** 78621081252  
**EAN Number:** 05414363151722  
**Status:** A

Non-Insulated Tubular Ring Terminal, Length 1.59 Inches, Width .69 Inches, Bolt Hole 1/4 Inch, Wire Range 2/2AN, Copper, Tin Plated, 100 Pack

- These non-insulated ring terminals are made of electrolytic copper for high conductivity.
- They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire).
- Application Tools: WT115A, TBM6, TBM6S, WT3185

### North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Type	Non-Insulated Ring Terminal
Special Features	These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire).
Standard	UL E9809
Wire Size	2 AWG
Voltage Rating	600 V
Material	Copper
Color	Metallic

### European Specifications (ETIM)

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	Straight
Slender flange model	N
Insulated	N
With sight-hole	Y
Material	Copper
Surface protection	Tinned
Number of fixing holes	1

### Packaging

Inner Quantity	100
Inner Dimensions (inches)	5x4.5x3
Outer Quantity	1000
Outer Dimensions (inches)	23.8x10.8x3.7
Weight Uom	3.5 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet US Available on Website

**For further technical assistance, please contact us...**

ABB Installation Products - USA  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120  
 www.tnb.com

ABB Installation Products Technical Support  
 MS 3B-50  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: techsupport@tnb.com