



Representative

Catalog Number: M972
Product ID: 7TAI029620R0114
UPC Number: 78621081627
EAN Number: 05414363155218
Status: A

Non-Insulated Tubular Ring Terminal, Length 2.28 Inches, Width 1.12 Inches, Bolt Hole 5/16 Inch, Wire Range 4/0AN-250kcmil, Copper, Tin Plated, 50 Pack

- These non-insulated ring terminals are made of electrolytic copper for high conductivity.
- They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire).
- Application Tools: TBM6, TBM6S, WT3185

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Non-Insulated Ring Terminal
Special Features	These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire).
Standard	UL E9809
Wire Size	4/0AN-250 kcmil
Voltage Rating	600 V
Material	Copper
Color	Metallic

European Specifications (ETIM)

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	Straight
Flange shape	Ring shape
Slender flange model	N
Insulated	N
Material	Copper
Surface protection	Tinned
Number of fixing holes	1

Packaging

Inner Quantity	50
Inner Dimensions (inches)	6x4x4
Outer Quantity	250
Outer Dimensions (inches)	21.5x7.1x4.9
Weight Uom	11.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000219
Technical Drawing / Data Sheet Canada	Available on Website

For further technical assistance, please contact us...

ABB Installation Products - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
 www.tnb.com

ABB Installation Products Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com