



## Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch
Device short name	XCKD
Sensor design	Compact
Body type	Fixed
Head type	Rotary head
Number of poles	2

## Complementary

Body material	Zamak
Head material	Zamak
Fixing mode	By the body
Movement of operating head	Rotary
Type of operator	Thermoplastic spring return roller lever (variable length)
Switch actuation	By 30° cam
Contacts insulation form	Zb
Positive opening min torque	0.25 N.m
Minimum torque for tripping	0.1 N.m
Maximum actuation speed	1.5 m/s
Repeat accuracy	0.1 mm on the tripping points with 1 million operating cycles
Contact code designation	A300, AC-15 (Ue = 240 V, Ie = 3 A) , Ithe = 10 A conforming to EN/IEC 60947-5-1 appendix A Q300, DC-13 (Ue = 250 V, Ie = 0.27 A) conforming to EN/IEC 60947-5-1 appendix A
Ui rated insulation voltage	300 V conforming to CSA C22-2 No 14 300 V conforming to UL 508 500 V degree of pollution 3 conforming to IEC 60947-1
Resistance across terminals	<= 25 mOhm conforming to IEC 60255-7 category 3
Uimp rated imp wstdvoltage	6 kV conforming to IEC 60664 6 kV conforming to IEC 60947-1
Short circuit protection	10 A by gG cartridge fuse
Electrical durability	5000000 cycles, DC-13 , 120 V 5000000 cycles, DC-13 , 24 V 5000000 cycles, DC-13 , 48 V
Mechanical durability	10000000 cycles
Width	31 mm
Height	65 mm
Depth	30 mm
Product weight	0.22 kg
CAD overall width	31 mm
CAD overall height	170 mm
CAD overall depth	40 mm
Terminals description ISO nT <sub>1</sub>	(13-14)NO (21-22)NC

## Environment

Material	Metal
Type of approach	2 directions lateral approach
Electrical connection	M12 male connector, 5 pins
Contacts type and composition	1 NC + 1 NO
Contacts operation	Snap action, break before make
Positive opening	With
Shock resistance	50 gn (duration = 11 ms) conforming to IEC 60068-2-27
Vibration resistance	25 gn (f = 10 - 500 Hz) conforming to IEC 60068-2-6
IK degree of protection	IK06 conforming to EN 50102
Class of prot agnst elec shock	Class I conforming to IEC 61140 Class I conforming to NF C 20-030
Ambient air temp for op	-25...70 °C
Ambient air temp for storage	-40...70 °C
Protective treatment	TC
Product certifications	CCC CSA UL
Standards	CSA C22-2 No 14 EN 60204-1 EN 60947-5-1 IEC 60204-1 IEC 60947-5-1 UL 508