

## Waber-by-Tripp Lite 10-Outlet Industrial Power Strip, 15-ft. Cord, Large Plug Spacing

MODEL NUMBER: **UL800CB-15**



### Highlights

- 10 outlets
- 15 ft. cord
- 17.5" length
- Lighted master switch
- All metal housing

### Package Includes

- UL800CB-15 Power Strip
- Warranty information
- Instruction manual

### Description

The Waber-by-Tripp Lite UL800CB-15 Power Strip offers reliable, convenient, cost effective method of power distribution for appliances, power tools, lighting and other electrical equipment. Includes 10 NEMA 5-15R output receptacles arranged with traditional wall socket spacing to accept large equipment plugs with minimal outlet blockage. Includes 15 foot AC line cord and flat sheet metal flanges for installation in a wide variety of applications. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Unfiltered electrical pass-through makes UL800CB-15 ideal for distributing alternate waveform UPS or generator power. Features rugged all-metal housing, lighted power switch, 15 amp resettable circuit breaker and attractive blue/gray color scheme. PLUG/OUTLETS - Input: NEMA 5-15P/Output: 10 NEMA 5-15R ELECTRICAL - 120VAC, 50/60Hz, 15A (Requires standard NEMA 5-15R wall receptacle) FORMAT - Corded power distribution strip

### Features

- Multi-outlet power strip offers reliable, convenient, cost effective method of power distribution for appliances, power tools, lighting and other electrical equipment.
- Includes 10 NEMA 5-15R output receptacles arranged with traditional wall socket spacing to accept large equipment plugs with minimal outlet blockage
- Lighted on/off switch controls power to all outlets
- Keyhole mounting tabs for installation in a wide variety of applications
- UL Recognized Component, Tested to UL1363 (Power Tap), cUL (Canada)
- 15 amp power handling capacity with circuit breaker
- 15 foot AC line cord

## Specifications



<b>OVERVIEW</b>	
UPC Code	037332117724
<b>OUTPUT</b>	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(10) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(5) Yes
Outlet Orientation	Two rows of 5 outlets
Right-Angle Outlets	No
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
Integrated Cord Clip	No
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	Lighted 2 position switch controls power to all outlets
<b>PHYSICAL</b>	
Anti-Microbial Protected	No
Color	Black
Color (AC Line Cord)	Black
Included Mounting Accessories	Keyhole slots on removable mounting brackets
Integrated Keyhole Mounting Slots	Yes (Includes flanges)
Keyhole Slot Mounting Measurement (Center to Center)	Distance between end tabs = 462.30mm
Material of Construction	Metal
Outlets Measurement (Center to Center)	Distance between horizontal outlets = 71.45mm; Distance between vertical outlets = 38.90mm
Receptacle Color	Black



Shipping Dimensions (hwd / cm)	6.35 x 22.86 x 51.44
Shipping Dimensions (hwd / in.)	2.50 x 9.00 x 20.25
Shipping Weight (kg)	2.27
Shipping Weight (lbs.)	5.00
Unit Dimensions (hwd / cm)	44.5 x 10.2 x 4.4
Unit Dimensions (hwd / in.)	17.5 x 4 x 1.75
<b>CERTIFICATIONS</b>	
UL1363 (Power Tap)	UL Recognized Component, Tested to UL1363 (Power Tap)
Canada	cUL
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>