


Shrink-Tag Markers

HellermannTyton's Shrink-Tag system is a heat shrink identification method which makes it easy to mark wire, cable, terminals, and other components.

For efficient marking, Shrink-Tags can be printed using HellermannTyton's thermal transfer printers. Shrink-Tag are also pin-fed for use with pin dot matrix printers. TagPrint software can be used with a standard dot matrix printer to print on the Shrink-Tag markers. Marks can also be made with a printer, typewriter, or pen. After the Shrink-Tag is heated and shrunk, the imprint is permatized and solvent resistant.

Shrink-Tag is self-extinguishing and recognized to UL standard for print performance, heat shock and flammability.

HellermannTyton also offers a military specified version of the Shrink-Tags, in both yellow and white, with or without perforations. When used with a dot matrix or HellermannTyton thermal transfer printer, these military specified Shrink-Tags meet Mil-I-23053/5, Class I and III, Mil. Std. 202 Method 215 (except solvent C because it is ozone depleting), and Mil-M- 81531 for print performance.



Material Specification - Shrink-Tag Markers

Material	Flexible, radiation cross-linked polyolefin
Shrink Ratio	3 : 1
Shrink Temperature	100°C
Operating Temperature	-30°C to +105°C
Mil Spec Version	-55°C to +135°C
Rating	600 Volts. Tensile Strength : 150 PSI
Packaging	250 markers per box. On a roll.
Specification	Flammability - UL.244 UL Recognized.
Mil Spec Version	Mil-M-81531 for print performance Mil-M-23053/5 Class I and III MIISTD 202 Method 215 (except solvent C)

Ordering Information and Technical Data

Part Number	A mm	B mm	C mm	D mm	E mm	As Supplied mm	Use Range mm	Wire Size AWG
THS-610BM	12.7	88.9	57.15	50.8	5.97	3.17	1.11-2.54	18-22
THS-610Y	12.7	88.9	57.15	50.8	5.97	3.17	1.11-2.54	18-22
THS-610YP	12.7	88.9	57.15	50.8	5.97	3.17	1.11-2.54	18-22
THS-610YM	12.7	88.9	57.15	50.8	5.97	3.17	1.11-2.54	18-22
THS-610YMP	12.7	88.9	57.15	50.8	5.97	3.17	1.11-2.54	18-22
THS-610W	12.7	88.9	57.15	50.8	5.97	3.17	1.11-2.54	18-22
THS-610WP	12.7	88.9	57.15	50.8	5.97	3.17	1.11-2.54	18-22
THS-610WM	12.7	88.9	57.15	50.8	5.97	3.17	1.11-2.54	18-22
THS-610WMP	12.7	88.9	57.15	50.8	5.97	3.17	1.11-2.54	18-22
THS-615BM	12.7	88.9	57.15	50.8	7.92	4.75	2.26-3.09	12-18
THS-615Y	12.7	88.9	57.15	50.8	7.92	4.75	2.26-3.09	12-18
THS-615YP	12.7	88.9	57.15	50.8	7.92	4.75	2.26-3.09	12-18
THS-615W	12.7	88.9	57.15	50.8	7.92	4.75	2.26-3.09	12-18
THS-615WP	12.7	88.9	57.15	50.8	7.92	4.75	2.26-3.09	12-18
THS-620BM	12.7	88.9	57.15	50.8	10.67	6.35	2.30-5.56	10-16
THS-620Y	12.7	88.9	57.15	50.8	10.67	6.35	2.30-5.56	10-16
THS-620YP	12.7	88.9	57.15	50.8	10.67	6.35	2.30-5.56	10-16
THS-620YM	12.7	88.9	57.15	50.8	10.67	6.35	2.30-5.56	10-16
THS-620YMP	12.7	88.9	57.15	50.8	10.67	6.35	2.30-5.56	10-16
THS-620W	12.7	88.9	57.15	50.8	10.67	6.35	2.30-5.56	10-16
THS-620WP	12.7	88.9	57.15	50.8	10.67	6.35	2.30-5.56	10-16
THS-620WM	12.7	88.9	57.15	50.8	10.67	6.35	2.30-5.56	10-16
THS-620WMP	12.7	88.9	57.15	50.8	10.67	6.35	2.30-5.56	10-16
THS-625BM	12.7	88.9	57.15	50.8	15.87	9.52	3.48-8.13	8-14
THS-625Y	12.7	88.9	57.15	50.8	15.87	9.52	3.48-8.13	8-14
THS-625YP	12.7	88.9	57.15	50.8	15.87	9.52	3.48-8.13	8-14
THS-625WM	12.7	88.9	57.15	50.8	15.87	9.52	3.48-8.13	8-14
THS-625W	12.7	88.9	57.15	50.8	15.87	9.52	3.48-8.13	8-14
THS-625WP	12.7	88.9	57.15	50.8	15.87	9.52	3.48-8.13	8-14
THS-630BM	12.7	88.9	57.15	50.8	21.00	12.70	4.65-10.79	2-10
THS-630Y	12.7	88.9	57.15	50.8	21.00	12.70	4.65-10.79	2-10
THS-630YP	12.7	88.9	57.15	50.8	21.00	12.70	4.65-10.79	2-10
THS-630YM	12.7	88.9	57.15	50.8	21.00	12.70	4.65-10.79	2-10
THS-630YMP	12.7	88.9	57.15	50.8	21.00	12.70	4.65-10.79	2-10
THS-630W	12.7	88.9	57.15	50.8	21.00	12.70	4.65-10.79	2-10
THS-630WP	12.7	88.9	57.15	50.8	21.00	12.70	4.65-10.79	2-10
THS-630WM	12.7	88.9	57.15	50.8	21.00	12.70	4.65-10.79	2-10
THS-630WMP	12.7	88.9	57.15	50.8	21.00	12.70	4.65-10.79	2-10
THS-635BM	12.7	88.9	57.15	50.8	30.48	19.05	8.00-18.42	6-0000
THS-635Y	12.7	88.9	57.15	50.8	30.48	19.05	8.00-18.42	6-0000
THS-635YP	12.7	88.9	57.15	50.8	30.48	19.05	8.00-18.42	6-0000
THS-635YM	12.7	88.9	57.15	50.8	30.48	19.05	8.00-18.42	6-0000
THS-635YMP	12.7	88.9	57.15	50.8	30.48	19.05	8.00-18.42	6-0000
THS-635W	12.7	88.9	57.15	50.8	30.48	19.05	8.00-18.42	6-0000
THS-635WP	12.7	88.9	57.15	50.8	30.48	19.05	8.00-18.42	6-0000
THS-635WM	12.7	88.9	57.15	50.8	30.48	19.05	8.00-18.42	6-0000
THS-635WMP	12.7	88.9	57.15	50.8	30.48	19.05	8.00-18.42	6-0000
THS-640Y	12.7	88.9	57.15	50.8	42.93	25.40	9.29-22.25	1-400
THS-640YP	12.7	88.9	57.15	50.8	42.93	25.40	9.29-22.25	1-400
THS-640YM	12.7	88.9	57.15	50.8	42.93	25.40	9.29-22.25	1-400
THS-640YMP	12.7	88.9	57.15	50.8	42.93	25.40	9.29-22.25	1-400
THS-640W	12.7	88.9	57.15	50.8	42.93	25.40	9.29-22.25	1-400
THS-640WP	12.7	88.9	57.15	50.8	42.93	25.40	9.29-22.25	1-400
THS-640WM	12.7	88.9	57.15	50.8	42.93	25.40	9.29-22.25	1-400
THS-640WMP	12.7	88.9	57.15	50.8	42.93	25.40	9.29-22.25	1-400

Y = Yellow

W=White

P=Perforated

M=Military Specified

B=Black