





NEVO SERIES c**FU**®us

OP3 **(€** ®


Patents pending

| | OUTPUT 3 SPECIFICA | TION | S | | |
|--|---|-------|-----|--------|---------|
| Parameter | Details | Min | Тур | Max | Units |
| Output voltage range | See table | 9 | 24 | 30 | ٧ |
| Rated current | | | | 7.5 | Α |
| Average output power | | | | 150 | Watts |
| Peak output power | See graph, < 5 seconds 50% duty cycle | | | 225 | Watts |
| Initial voltage accuracy | Factory set units | -0.5 | | 0.5 | % |
| Manual Voltage Adjust | 11 turn potentiometer | | 1.9 | | V/turn |
| Load Regulation | Measured at sense terminals | -150 | | 150 | mV |
| Line Regulation | Measured at sense terminals | -0.1 | | 0.1 | %Vnom |
| Cross Regulation | Measured at sense terminals | -0.2 | | 0.2 | %Vnom |
| Minimum Load | | | | 0 | Watts |
| Temperature coefficient | | -0.02 | | 0.02 | %/°C |
| Ripple and Noise | 20MHz BW, pk-pk | | | 1 | %Vnom |
| | 25% to 75% load transient at 0.25A/uS | | | 3 | V |
| Transient response | Recovery to within 10% of Vset | | | 100 | uS |
| Turn on rise time | Monotonic 10% to 90% | 1.5 | | 3.5 | mS |
| Turn on overshoot | | | | 0.1 | %Vset |
| T an dala | AC to PG | | 600 | 750 | mS |
| Turn on delay | En to PG | | 15 | 20 | mS |
| Current share accuracy | | | | 5 | %Imax |
| Open sense offset | Open sense, voltage offset due to bias currents | | | 2 | %Vnom |
| Holdup voltage | | | | 25 | ٧ |
| Isolation to ground | Each terminal | | | 250 | ٧ |
| Over current protection | % of rated current | 105 | | 125 | %rated |
| Reverse current protection | % of rated current | -6 | | 0 | %rated |
| Short circuit | Period | | 125 | | mS |
| protection (Hiccup | Duty cycle | | 3 | | % |
| mode) | Voltage threshold (Measured | | 3.5 | | V |
| 0 | at sense terminals) | | | | - |
| Over voltage protection | Latching | | 36 | | ٧ |
| Over Temperature protection | Internally monitored. Latching | 115 | | 125 | °C |
| Sense cable protection | Positive Negative | -1 | | 2 1 | V |
| Power Good threshold | Low threshold only | | 90 | _ | %Vset |
| Current output signal | I _{SIG} =0.6+I _{OUT} /(I _{RTD} *1.25) | 0 | | 110 | %Irated |
| Current limit control | $I_{LMT} = (V_{CTRL} - 0.6) * I_{RTD} * 1.25$ | 0 | | 110 | %Irated |
| Remote voltage control | V _{OUT} =V _{SET} ((1.8-V _{CTRL})/0.6) | 0 | | 300 | %Vset |
| Bias supply | 10mA max | 4.5 | 5 | 5.2 | V |
| Reliability | 40°C 80% load | | | 1 | FPMH |
| Warranty | | | | 2 | Years |
| Wire Size | | 20 | 18 | 10 | AWG |
| Weight | | | | 60 | Grams |
| Size | 60mm x 35mm x 17mm | | | | |
| Notes: All specifications are believed to be correct at time of publication and are subject to | | | | | |









Vox Power Ltd. reserves the right to change or improve any part of the specification, electrical or mechanical design or manufacturing process without notice. Please consult your local distributor or contact Vox Power to ensure that you have the latest specification before using your product. For other information relating to the use of the product please refer to the latest NEVO user manual. Vox Power reserves the right to make changes without notice to any of its products. Vox Power does not assume any liability arising out of the use or application of any of its products and of any information to the maximum extent permitted by law. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vox Power. VOX POWER DISCLAIMS ALL WARRANTIES AND REPRESENTATIONS. IN PARTICULAR ALL OTHER WARRANTIES, CONDITION OR TERMS RELATING TO SUITABILITY, FITNESS FOR PURPOSE, MECHANTABILITY OR CONDITION OF THE PRODUCTS AND WHETHER EXPRESS OR IMPLIED BY STATURE OR COMMON LAW OR OTHERWISE ARE EXCLUDED.

Document DOC6004 rev 02

Vox Power Ltd. Unit 9 Robinhood Business Park Robinhood Road, Ballymount Dublin 22, Ireland

Tel: +353 1 426 4930, Fax: +353 1 633 5511

Web: ww.vox-power.com

change without notice.