


RoHS Compliant

BOMcheck.net

Color: ■



Item description

The 852-1111 is a 5-port 1000Base-T industrial ETHERNET switch supporting Auto-Negotiation and Auto-MDI-/MDI-X detection for each port.

Using the switch's 5 ports, several segments can be created to reduce the network load, while providing a dedicated bandwidth to each user node. The 852-1111 Switch is a cost-effect solution to keep up with the constant demands of IP-based, industrial communication needs.

The switch is easy to configure and install and is best suited for small to medium-sized networks.

Features:

- 5 ETHERNET Ports, 10/100/1000 Mbps autonegotiation
- Front-panel diagnostic LEDs
- Supports Auto-MDI/MDI-X functions
- Full/half-duplex transfer modes for each port
- Store-and-forward switching method
- Integrated address look-up table, supports up to 8000 absolute MAC addresses
- Overvoltage protection
- IEEE 802.3x flow control in full-duplex mode
- Prioritization of Profinet Ethernet Frame (EtherType=0x8892) according to IEEE802.1p
- DIN-35 rail mounting



Data

Technical Data

Switchingmodus	Store-and-forward, non-blocking
Number of 1000Base-T ports	5
Communication standards	IEEE 802.3 10BASE-T IEEE 802.3u 100BASE-TX IEEE 802.3ab 1000BASE-T IEEE 802.3x Flow Control IEEE 802.1p Prioritization
MAC table (large)	8000 addresses
Jumbo frame size	9000 Byte
Supply voltage	DC 9 ... 48 V
Energy consumption max.	3 W
Baud rate	Copper cable: 10/1000Mbit/s
Transmission medium (communication/fieldbus)	Copper cable: Cat. 5 or higher, 100 m maximum cable length
Topology	Star
Indicators	Device: LED (PWR) green: Power supply; per port: LED (100, 1000) green: Status 100 Mbps, 1000 Mbps port 1 ... 5

Connection data

Connection technology: communication/fieldbus	Copper cable: 5 x RJ-45
Anschluss technik: Versorgung	1 x im Gerät verbaute Stiftleiste: 231-433/001-000; mitgelieferte Federleiste (Steckverbinder MCS): 231-103/026-000

Geometrical Data

Width	23.4 mm / 0.921 inch
Height from upper-edge of DIN-35 rail	81 mm / 3.189 inch
Depth	109.2 mm / 4.299 inch

Mechanical data

Weight	190 g
Color	black
Housing material	Sheet steel
Conformity marking	CE

Environmental Requirements

Surrounding air (operating) temperature	-40 ... 70 °C
Surrounding air (storage) temperature	-40 ... 80 °C
Degree of protection	IP30
Relative air humidity (no condensation)	95 %
Type of mounting	DIN-35 rail


Vibration resistance	acc. to IEC 60068-2-6
Shock resistance	acc. to IEC 60068-2-27

Commercial data

Country of origin	TW
GTIN	4050821808916
Customs Tariff No.	85176200000
Product Group	27 (Special components I/O)


Approvals / Certificates

Ship Approvals





Logo	Approval	Certificate name
	DNV DNV Germany GmbH	A-14050

Compatible products




General accessories















	Item no.: 852-9101 DNV Carrier rail adapter; for ETHERNET Switches 852-111/ 852-1111 marine approval	www.wago.com/852-9101
--	--	--

transfer module

	Item no.: 289-172 Interface module for ETHERNET RJ-45	www.wago.com/289-172
	Item no.: 289-175 Interface module for ETHERNET RJ-45	www.wago.com/289-175
	Item no.: 289-195 Interface module for ETHERNET RJ-45; for DIN 35 rail; with shield connection	www.wago.com/289-195
	Item no.: 289-196 Interface module with RJ-45 connectors; CAGE CLAMP®CONNECTION; with LED; Fused	www.wago.com/289-196








wiring and connectors

	Item no.: 750-975 ETHERNET RJ-45 connector, IP20; ETHERNET 10/100 Mbit/s; for field assembly	www.wago.com/750-975
	Item no.: 750-976 PROFINET RJ-45 connector, IP20; ETHERNET 10/100 Mbit/s; for field assembly	www.wago.com/750-976
	Item no.: 750-977/000-011 Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568A; AWG 22	www.wago.com/750-977/000-011

	<p>Item no.: 750-977/000-012 Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568B; AWG 22</p>	www.wago.com/750-977/000-012
	<p>Item no.: 750-977/000-013 Connector PROFINET; RJ-45; Cat. 6A; straight; AWG 22</p>	www.wago.com/750-977/000-013
	<p>Item no.: 750-977/000-021 Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568A; AWG 24</p>	www.wago.com/750-977/000-021
	<p>Item no.: 750-977/000-022 Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568B; AWG 24</p>	www.wago.com/750-977/000-022
	<p>Item no.: 750-978/000-011 Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568A; AWG 22; Strain relief</p>	www.wago.com/750-978/000-011
	<p>Item no.: 750-978/000-012 Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568B; AWG 22; Strain relief</p>	www.wago.com/750-978/000-012
	<p>Item no.: 750-978/000-013 Connector PROFINET; RJ-45; Cat. 6A; straight; AWG 22; Strain relief</p>	www.wago.com/750-978/000-013
	<p>Item no.: 750-978/000-021 Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568A; AWG 24; Strain relief</p>	www.wago.com/750-978/000-021
	<p>Item no.: 750-978/000-022 Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568B; AWG 24; Strain relief</p>	www.wago.com/750-978/000-022
	<p>Item no.: 750-979/000-011 Connector ETHERNET; RJ-45; Cat. 6A; angled; Code T568A; AWG 22; Strain relief</p>	www.wago.com/750-979/000-011
	<p>Item no.: 750-979/000-012 Connector ETHERNET; RJ-45; Cat. 6A; angled; Code T568B; AWG 22; Strain relief</p>	www.wago.com/750-979/000-012
	<p>Item no.: 750-979/000-013 Connector PROFINET; RJ-45; Cat. 6A; angled; AWG 22; Strain relief</p>	www.wago.com/750-979/000-013
	<p>Item no.: 750-979/000-021 Connector ETHERNET; RJ-45; Cat. 6A; angled; Code T568A; AWG 24; Strain relief</p>	www.wago.com/750-979/000-021
	<p>Item no.: 750-979/000-022 Connector ETHERNET; RJ-45; Cat. 6A; angled; Code T568B; AWG 24; Strain relief</p>	www.wago.com/750-979/000-022

power supply



	Item no.: 787-1102 Switched-mode power supply; Compact; 1-phase; 24 VDC output voltage; 1.3 A output current; DC OK signal	www.wago.com/787-1102
	Item no.: 787-1112 Switched-mode power supply; Compact; 1-phase; 24 VDC output voltage; 2.5 A output current; DC OK signal	www.wago.com/787-1112
	Item no.: 787-1122 Switched-mode power supply; Compact; 1-phase; 24 VDC output voltage; 4 A output current; DC OK signal	www.wago.com/787-1122
	Item no.: 787-1226 Switched-mode power supply; Compact; 1-phase; 24 VDC output voltage; 6 A output current	www.wago.com/787-1226
	Item no.: 787-1702 Switched-mode power supply; Eco; 1-phase; 24 VDC output voltage; 1.25 A output current	www.wago.com/787-1702
	Item no.: 787-1712 Switched-mode power supply; Eco; 1-phase; 24 VDC output voltage; 2.5 A output current	www.wago.com/787-1712
	Item no.: 787-1722 Switched-mode power supply; Eco; 1-phase; 24 VDC output voltage; 5 A output current	www.wago.com/787-1722

Downloads

Documentation

Manual

5-Port 1000BASE-T Industrial ECO Switch	Dec 6, 2016	990.3 kB	Download
---	-------------	----------	----------

Bid Text

852-1111	Jan 21, 2016	DOC 28.7 kB	Download
----------	--------------	----------------	----------

Additional Information

Disposal; Electrical and electronic equipment, Packaging	Oct 15, 2018	265.8 kB	Download
--	--------------	----------	----------

System Description

Industrial Switches – General Product Information	Jun 6, 2017	514.9 kB	Download
---	-------------	----------	----------

CAD/CAE - Smart Data

CAD data

3D Download 852-1111	URL	Download
----------------------	-----	----------



Subject to changes.

WAGO Kontakttechnik GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.