

**Cable glands**  
**VG 16-MS54**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



An economical plastic cable gland, such as you often find in industrial applications. With their soft rubber seal, they offer a secure fit for the cable and a good IP protection degree (IP 54). In addition, the nickel-plated brass gives you good corrosion protection from external influences.

**General ordering data**

Order No.	<a href="#">026140000</a>
Type	VG 16-MS54
Version	Cable glands, Cable gland, Brass, nickel-plated, PG 16
GTIN (EAN)	4008190118624
Qty.	50 pc(s).

**Cable glands  
VG 16-MS54**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Length	27 mm	Net weight	28.4 g
--------	-------	------------	--------

**General information**

AF size 1	22 mm	AF size 2	24 mm
Cable gland	PG	Clamping range, bolted connection , max.	14 mm
Clamping range, min. test adapter	12 mm	DIN	DIN 46320 / C4
External thread	PG 16	Length of thread	6.5 mm
Material	Brass, nickel-plated	Operating temperature range, max.	60 °C
Operating temperature range, min.	-20 °C	Protection degree with GWDR	IP 65
Seal insert	NBR	Torque for cap nut, max.	15 Nm
Torque for cap nut, min.	15 Nm	Torque for connecting adapter, max.	22.5 Nm
Torque for connecting adapter, min.	22.5 Nm		

**Classifications**

ETIM 2.0	EC000441	ETIM 3.0	EC000441
UNSPSC	30-21-18-01	eClass 4.1	27-14-12-09
eClass 5.1	27-14-91-09	eClass 6.0	27-14-91-09
eClass 7.0	27-14-91-09		

**Approvals**

Approvals

