

Industrial Ethernet IE-SW-BL05-4TX-1SC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Product image



- Variations with 5 or 8 ports
- Variations for Gigabit Ethernet
- Sturdy metal housing
- Compact design
- Two redundant power inputs 12/24/48 V DC
- Variations with copper and fibre-optic interface (multimode and singlemode)
- Extensive approvals: CE, FCC, cULus, Class I Div. 2 / ATEX Zone 2, DNV-GL

General ordering data

Type	IE-SW-BL05-4TX-1SC
Order No.	1240890000
Version	Network switch, unmanaged, Fast Ethernet, Number of ports: 4 x RJ45, 1 * SC Multi-mode, IP30, -10 °C...60 °C
GTIN (EAN)	4050118028669
Qty.	1 pc(s).

**Industrial Ethernet
IE-SW-BL05-4TX-1SC**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Width	30 mm	Width (inches)	1.181 inch
Height	115 mm	Height (inches)	4.528 inch
Depth	70 mm	Depth (inches)	2.756 inch
Net weight	175 g		

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

EMC conformity and approvals

EMC standards	EN 55032, EN 55024, CISPR 32, FCC Part 15 Subpart B Class A, IEC 61000-4-2 ESD: Contact: 6 kV; Air: 8 kV, IEC 61000-4-3 RS: 80 MHz to 1 Ghz: 10 V/m, IEC 61000-4-4 EFT: Power: 2 kV; Signal: 1 kV, IEC 61000-4-5 Surge: Power: 2 kV; Signal: 2 kV, IEC 61000-4-6 CS: 10 V, IEC 61000-4-8	Explosive risk zone	UL/cUL, Class I, Division 2, Groups A, B, C and D, ATEX Zone 2 Ex nA IIC T4 Gc
Free fall	According to IEC 60068-2-32	Ship use	DNV-GL
Shock	according to IEC 60068-2-27	Vibration	according to IEC 60068-2-6

Environmental conditions

Humidity	5 to 95 % (non-condensing)	Operating temperature, max.	60 °C
Operating temperature, min.	-10 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C		

Fibre optic transceiver characteristics

Transmission rate	100 Mbps	
Transceiver type	Multimode	
Connector type	SC-Duplex	
Transmission distance, typ.	5 km	
Wavelength	typ.	1,300 nm
	Wavelength	TX
	min.	1,260 nm
	max.	1,360 nm
	Wavelength	RX
	min.	1,100 nm
Receive power	min.	-32 dBm
	max.	-3 dBm
Transmission power	min.	-20 dBm
	max.	-10 dBm
Link-budget	12 dB	

**Industrial Ethernet
IE-SW-BL05-4TX-1SC**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Guarantee**

Time interval	5 years
---------------	---------

Interfaces

DIP switch	1x for enabling/disabling the broadcast storm protection	Fibre-optic ports	100BaseFX ports (SC connector), Multimode
LED indicator	PWR1, PWR2, 10/100M (TP-Port), 100M (fibre-optic port).	Number of ports	4 x RJ45, 1 * SC Multimode
RJ45 ports	10/100BaseT(X), auto negotiation, Full-/half-duplex mode, Auto MDI/MDI-X port		

MTBF

MTBF	3,040,784 hrs	Database	Telcordia (Bellcore), GB
------	---------------	----------	--------------------------

Power supply

Connection type	1 removable 4-pin terminal block		
Current consumption	0.11 A at 24 V		
Overload current protection	1.1 A		
Reverse polarity protection	Available		
Voltage supply	12/24/48 V DC, 2 redundant inputs		
Voltage supply range	Voltage type	DC	
	Voltage, min.	9.6 V	
	Voltage, max.	60 V	

Switch characteristics

Bandwidth backplane	1 Gbps	MAC table size	1 K
Packet buffer size	512 Kbit		

Technical data

Housing main material	Aluminium	Protection degree	IP30
Type of mounting	DIN rail, Panel (with optional mounting kit)		

Technology

Data switching	Store and Forward	Flow control	IEEE 802.3x flow control, Back pressure flow control
Standard	IEEE 802.3 for 10BaseT, IEEE 802.3u for 100BaseT(X) and 100BaseFX, IEEE 802.3x for flow control		

Classifications

ETIM 6.0	EC000734	ETIM 7.0	EC000734
eClass 9.0	19-17-01-06	eClass 9.1	19-17-01-06
eClass 10.0	19-17-04-02		

Creation date January 24, 2020 6:05:02 PM CET

Data sheet

**Industrial Ethernet
IE-SW-BL05-4TX-1SC**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Downloads

Approval/Certificate/Document of Conformity	DNV-GL certificate ATEX certificate KC certificate EU Declaration of Conformity
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP
Product Change Notification	Product Change Notification IE-SW-BL05-series
User Documentation	Hardware Installation Guide