


RS-SERIES

RS 30 24VDC BL/SL 1U

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Product image



Similar to illustration

Clip-on RS 30. 31. 32 relay bases are available in widths from 11.2 to 25 mm, depending on the type. The RSM relay multiplexers are available as 4, 8 and 16-way modules. To reduce the wiring work, the DC variants are fitted with a common plus or minus potential. The optional IEC603-1 plug-in connector enables the connection of pre-assembled lines. The screw connection system is used to connect the conductor with a rated cross-section of 2.5 mm².

General ordering data

Delivery status	Discontinued
Available until	2017-12-15
Type	RS 30 24VDC BL/SL 1U
Order No.	1100260000
Version	RS-SERIES, Relay module, Number of contacts: 1 CO contact AgNi 0.15 gold flashed, Rated control voltage: 24 V DC ±10 %, Continuous current: 6 A, Screw connection
GTIN (EAN)	4008190119089
Qty.	10 pc(s).
Alternative product	1122770000
Creation date April 12, 2020 11:17:38 PM CEST	

RS-SERIES
RS 30 24VDC BL/SL 1U

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Width	11.2 mm	Width (inches)	0.441 inch
Height	74 mm	Height (inches)	2.913 inch
Depth	56 mm	Depth (inches)	2.205 inch
Net weight	34.1 g		

Temperatures

Humidity	40 °C / 93 % rel. humidity, no condensation	Operating temperature, max.	40 °C
Operating temperature, min.	-25 °C	Storage temperature, max.	60 °C
Storage temperature, min.	-40 °C	Operating temperature	-25 °C...40 °C
Storage temperature	-40 °C...60 °C		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Input

Rated control voltage	24 V DC \pm 10 %	Rated current DC	10 mA
Power rating	0.45 W	Pull-in/drop-out voltage, typ.	21.5 V DC
Pull-in/drop-out current, typ.	12 mA / 3 mA DC	Status indicator	No
Protective circuit	Free-wheeling diode, Reverse polarity protection		

Output

Rated switching voltage	250 V AC	Max. switching voltage, AC	250 V
Continuous current	6 A	Inrush current	8 A
AC switching capacity (resistive), max.	2000 VA	Switch-on delay	\leq 8 ms
Switch-off delay	\leq 7 ms	Duration of Bounce	\leq 3 ms
Min. switching power	250 mW	Max. switching frequency at rated load	0.1 Hz

Contact data

Contact type	1 CO contact (AgNi 0.15 gold flashed)	Electrical service life of AC coil	$> 7 \times 10^5$ Switching cycles
Electrical service life, DC coil	$> 5 \times 10^5$ switching cycles	Mechanical service life	20×10^6 switching cycles

General data

Version	soldered relay	Rail	TS 32, TS 35
Test button	No	Mechanical switch position indicator	No
Colour	orange		

Insulation coordination

Rated voltage	250 V	Surge voltage category	III
Pollution severity	2	Protection degree	IP20
Creepage and clearance distance input - output	> 3 mm	Impulse withstand voltage	4 kV

Further details of approvals / standards

Standards	DIN EN 50178	Certificate No. (CSA)	082859-C-000
-----------	--------------	-----------------------	--------------

Creation date April 12, 2020 11:17:38 PM CEST

Data sheet

**RS-SERIES
RS 30 24VDC BL/SL 1U**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Connection data

Wire connection method	Screw connection	Stripping length, rated connection	8 mm
Clamping range, rated connection	2.5 mm ²	Clamping range, min.	0.5 mm ²
Clamping range, max.	4 mm ²		

Classifications

ETIM 6.0	EC001437	ETIM 7.0	EC001437
eClass 9.0	27-37-16-01	eClass 9.1	27-37-16-01
eClass 10.0	27-37-16-01	UNSPSC	30-21-19-17

Approvals

Approvals



ROHS Conform

Downloads

Approval/Certificate/Document of Conformity	DE_PA_5600_160311_001.pdf
Engineering Data	EPLAN, WSCAD