

Accessories
VGM32-MS68 15-25 BG

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



With blueglobe®, Weidmüller has introduced a cable gland from Pflitsch into its portfolio that convinces both in terms of reliability and functionality.

A large sealing range from 1.5 to 77 mm thanks to removable inlets with just 11 cable glands, highly effective sealing, excellent strain relief and a groove-guided upstream O-ring – these are the features of the blueglobe® cable glands which Weidmüller offers in brass and stainless steel.

The heart of the blueglobe® cable gland is the spherical seal insert that squeezes the cable gently and over a large area. This permanently avoids the incisive notch effect that is common with lamella systems.

General ordering data

Type	VGM32-MS68 15-25 BG
Order No.	1193610000
Version	Heavy-duty connectors, Accessories, Cable glands, Brass, nickel-plated
GTIN (EAN)	4032248976621
Qty.	25 pc(s).

Accessories VGM32-MS68 15-25 BG

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Length	40 mm	Length (inches)	1.575 inch
Net weight	112.88 g		

Temperatures

Limit temperature	-40 °C ... 130 °C
-------------------	-------------------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

General data

AF size	36 mm	Cable diameter, max.	25 mm
Cable diameter, min.	15 mm	Cable glands	M 32
External thread	M 32	Length of thread	8 mm
Material	Brass, nickel-plated	O-Ring	NBR
Protection degree	IP68 - 15 bar	Sealing material	T80s
Tightening torque, max.	15 Nm	Type of sealing	Rubber ring
UL 94 flammability rating	V-0		

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
eClass 9.0	27-14-44-32	eClass 9.1	27-14-44-32
eClass 10.0	27-14-44-32		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN CAT 5 ENCL 17/18 EN FL FIELDWIRING EN
Engineering Data	EPLAN
Engineering Data	STEP