

I-Series, Accessories
ITA 1/ZA

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The clip-on test adapter ITA is used as a single thin element and as a test adapter strip for measurements in electrical cabinets. Conductors with cross-sections from 0.5 mm² to 1.0 mm² can be connected. The test adapter simply clips onto the terminal and thus guarantees reliable contact with the live busbar.

General ordering data

Type	ITA 1/ZA
Order No.	1803810000
Version	I-Series, Accessories, Test adapter, Black, 6.9 mm
GTIN (EAN)	4032248303830
Qty.	25 pc(s).

I-Series, Accessories
ITA 1/ZA

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Length	27 mm	Width	6.9 mm
Height	75.5 mm	Net weight	8.28 g

Temperatures

Operating temperature		Storage temperature	
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

Additional technical data

Installation advice	Direct mounting	Version	For the terminals
---------------------	-----------------	---------	-------------------

Clampable wires (rated connection)

Type of connection	Screw connection	Stripping length	6 mm
Tightening torque, min.	0.3 Nm	Tightening torque, max.	0.3 Nm
Wire connection cross section, solid core, max. rated connection	0.5 mm ²	Wire connection cross section, solid core max. rated connection	1 mm ²
Wire connection cross section, finely stranded, max.	1 mm ²	Wire connection cross-section, finely stranded, min.	0.5 mm ²

Rated data

Rated cross-section	1 mm ²	Rated voltage	500 V
Rated current	12 A		

Material data

Material	Wemid	Colour	Black
UL 94 flammability rating	V-0		

System specifications

Product family	I-Series, Accessories	Type of connection	Screw connection
----------------	-----------------------	--------------------	------------------

Classifications

ETIM 3.0	EC002255	UNSPSC	30-21-18-01
eClass 6.2	27-14-92-14	eClass 7.1	27-14-92-14

Approvals

Approvals



ROHS Conform