

Discrete Relays

910003

When good enough just isn't good enough

Weidmüller 
RS 21 A, Combi-foot, TS 35/32
[Email to a Friend](#)


Representative Photo

Technical Information

Rail Type	Combi Foot
Input Voltage	24 VDC
Module Type	Socket Only
Number of Channels	1
Contact Current/Resistive Load (continuous in Amps)	10 A
Relay Contact Type	DPDT Form C
Plug-In Relay Type	8-Pin Octal
Housing Type	RS 21A

Additional Data

Voltage Output	250 V
Continuous Current for Resistive Loads	10 A
Contact Arrangement (Style)	DPDT
Storage Temperature Range	-40°C...+60°C
Operating Temperature Range	-25°C...+40°C
Wire Size	#22...14 AWG 0.5...2.5 mm ²
Clamp Screw Tightening Torque Nm (lb.in.)	0.4 (3.50)
Mechanical Dimensions (WxLxH) mm (in.)	39.6/70.3/45.7 (1.56"/2.77"/1.8")
Insulation Stripping Length mm (in.)	7 (.28")

Suggested Accessories

DIN-rail
 End bracket
 Ferrules
 Markers (SchT)
 Marking pens
 Marking tags (DEK)
 Mounting brackets
 Replacement relay

Tools

Product Liability The above information describes our products. It does not constitute guaranteed properties and is not intended to affirm the suitability of a product for a particular application. Regrettably, omissions and exceptions cannot be completely ruled out. Technical data are always specified by their average values. Exact data and the tolerances which apply to our processes can be requested from:

Weidmüller - North America

United States 001 (800) 849-9343

Canada 001 (800) 268-4080

or

Weidmüller - Germany

Telephone operator 0049 (-5252) 960-0