

**Pressing tool
PZ ZH 16****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Crimping tools for wire end ferrules, with and without plastic collars**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Type	PZ ZH 16
Order No.	9013600000
Version	Pressing tool, Crimping tool for wire-end ferrules, 6mm ² , 16mm ² , Indent crimp
GTIN (EAN)	4032248065523
Qty.	1 pc(s).

Creation date August 18, 2020 9:49:18 AM CEST

Catalogue status 14.08.2020 / We reserve the right to make technical changes.

Data sheet

**Pressing tool
PZ ZH 16**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	250 mm	Width (inches)	9.842 inch
Weight	730 g	Net weight	674.78 g

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Technical data

Version	Mechanical, without interchangeable inserts
---------	---

Description of contact

Type of contact	Twin wire-end ferrules	Crimping range, min.	6 mm ²
Crimping range, max.	16 mm ²	Conductor cross-section, max. AWG	AWG 6
Conductor cross-section, min. AWG	AWG 10		

tool data crimping

Crimping profile 1, min.	6 mm ²	Crimping type/profile	Indent crimp
Wire end ferrules cross-section, min.	6 mm ²	Wire end ferrules cross-section, max.	16 mm ²
Crimping profile 2, min.	10 mm ²	Crimping profile 3, min.	16 mm ²

Classifications

ETIM 6.0	EC000168	ETIM 7.0	EC000168
eClass 9.0	21-04-38-11	eClass 9.1	21-04-38-11
eClass 10.0	21-04-38-11	UNSPSC	31-16-31-02

Approvals

Approvals



Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	WSCAD
User Documentation	Manual

Data sheet

Pressing tool
PZ ZH 16

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Example of use

